

WSH 5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

The comprehensive accessories of the Klippon® Connect portfolio are perfectly matched down to the last detail. This facilitates mounting while adhering to required norms

General ordering data

Version	Accessories, Rail support, Wemid
Order No.	1080100000
Type	WSH 5
GTIN (EAN)	4008190965143
Qty.	10 items

WSH 5

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	39 mm	Depth (inches)	1.5354 inch
Height	99 mm	Height (inches)	3.8976 inch
Width	8 mm	Width (inches)	0.315 inch
Net weight	9.75 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
Operating temperature	-50 °C...120 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	120 °C		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	Wemid	Colour	dark beige
UL 94 flammability rating	V-0		

System specifications

Version	For the mounting rails	Mounting rail	TS 35
---------	------------------------	---------------	-------

Additional technical data

Type of fixing	when screwed in	Installation advice	Direct mounting
Explosion-tested version	No	Type of mounting	Snap-on

Dimensions

Pitch in mm (P)	8.00 mm	Mounting offset	56 mm
-----------------	---------	-----------------	-------

General

Number of poles	1	Installation advice	Direct mounting
Mounting rail	TS 35		

Classifications

ETIM 8.0	EC001166	ETIM 9.0	EC001166
ETIM 10.0	EC001166	ECLASS 14.0	27-40-06-07
ECLASS 15.0	27-40-06-07		