

HDC IP68 10B AS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The new RockStar® enclosures are resistant to seawater and offer a high degree of shock resistance, meet IP 68 and IP 69K, and have been developed for use under extreme environmental conditions and designed for the high vibration requirements acc. to DIN EN 61373 cat. 2 (bogie). As such, this housing family is ideally suited for fault- and maintenance-free operation of heavy-duty connectors in transport and traffic engineering as well as in power engineering and in applications with extreme requirements. During development, measures were also implemented to make the enclosures extremely EMC-resistant.

General ordering data

Version	HDC enclosures, Installation size: 4, Protection degree: IP66, IP68, IP69, in plugged condition, Bulkhead housing, Clamping yoke connection, Standard, Size of cable entries: none
Order No.	1081520000
Type	HDC IP68 10B AS
GTIN (EAN)	4032248844272
Qty.	1 items

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Height	29.5 mm	Height (inches)	1.1614 inch
Width	58 mm	Width (inches)	2.2835 inch
Mounting dimension - height	32 mm	Mounting dimension - width	83 mm
Net weight	170 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption		
REACH SVHC	No SVHC above 0.1 wt%		
Chemical resistance	Substance	Acetone	
	Chemical resistance	Resistant	
	Substance	Diesel oil	
	Chemical resistance	Unstable	
	Substance	Ethyl alcohol	
	Chemical resistance	Resistant	
	Substance	Transmission oil	
	Chemical resistance	Conditionally resistant	
	Substance	Hydraulic oil	
	Chemical resistance	Conditionally resistant	
	Substance	Petroleum benzine	
	Chemical resistance	Unstable	
	Substance	Sweat	
	Chemical resistance	Conditionally resistant	
	Substance	Premium gasoline	
	Chemical resistance	Unstable	
	Substance	Water	
Chemical resistance	Resistant		
Substance	UV		
Chemical resistance	Resistant		
Substance	Ozone		
Chemical resistance	Resistant		

Dimensions

Hole pitch length A2	83 mm	Cable entry	No
Total length housing	144 mm		

General data

Surface finish	Powder coating	Protection degree	IP66, IP68, IP69, in plugged condition
----------------	----------------	-------------------	--

Version

Number of cable glands	0	Size of cable entries	none
Top part/bottom part/lid	lower part	Cover	without cover

HDC IP68 10B AS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Number of cable entry on top	0	Number of cable entry sideways	0
Design of housing	Bulkhead housing	Design of locking system	Clamping yoke connection
Design	Standard	Installation size	4
Cable entry	No	Type	Bulkhead (feed-through)
Clamp version	Clamping yoke connection	Sealing	Silicone
Internal thread	without	Colour (RAL)	RAL 9011, RAL 9005
BG	4	Suitable for ModuPlug®	Yes

Important note

Product information When mounting the housings, make sure that the flat gasket is correctly seated.

Classifications


ETIM 8.0	EC000437	ETIM 9.0	EC000437
ETIM 10.0	EC000437	ECLASS 14.0	27-44-02-02
ECLASS 15.0	27-44-02-02		

HDC IP68 10B AS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com



HDC IP68 10B AS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Flange seals



We offer a variety of accessories, including seals, to accompany the housings. Because of the excellent sealing, you can achieve the best seal possible with our housings. Extensive testing has confirmed it – RockStar® remains impermeable to water to a depth of 50 metres This allows you to use heavy-duty connectors in environments which previously required fixed-wire installation.

General ordering data

Type	HDC FLDG 10B IP68	Version	
Order No.	1987500000	Accessories, Enclosures accessories	
GTIN (EAN)	4050118379211		
Qty.	10 ST		

IP68 O-ring seals



We offer a variety of accessories, including seals, to accompany the housings. Because of the excellent sealing, you can achieve the best seal possible with our housings. Extensive testing has confirmed it – RockStar® remains impermeable to water to a depth of 50 metres This allows you to use heavy-duty connectors in environments which previously required fixed-wire installation.

General ordering data

Type	HDC DG 10B IP68	Version	
Order No.	1987510000	Accessories, Enclosures accessories	
GTIN (EAN)	4050118379228		
Qty.	10 ST		