

KDSU M75 BN O NI 1 G75S**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Similar to illustration

The KDSU features a special ring in the shape of a truncated cone. The ring enables connections between single-wire-armoured and metal-foil-armoured cables and braided-armoured lines. This ensures a conductive connection between the cable and the cable gland. It is also possible to connect non-armoured cables and lines. In addition, the KDSU comes with two separate seals which provide sealing for the outer and inner parts of the cable insulation. The cable armouring is located between the inner and outer insulation. When the cable gland is ordered together with a neoprene seal, the seal allows temperatures from -35°C to +90°C. When using a silicone seal, a temperature range of -60°C to +180°C is possible. The O-ring and the cable gland included in the delivery are made from the same material. When using both sealing materials, IP66 or IP68 protection at a depth of 25 metres under water (a pressure of 2.5 bar) is guaranteed. The KDSU is permitted for use with pressure-resistant Ex d encapsulations and increased safety Ex e. Besides the mechanical protective function offered for cables and lines, this can also be used for EMC applications.

General ordering data

Version	KDSU (Klippon double seal universal Ex cable gland), Cable glands, straight, M 75, 19 mm, Single-wire armouring, Metal foil armouring, Braided armouring, 0.1 - 2.5 mm, OD min. 60.2 - OD max. 68 mm, ID min. 52.10 - ID max. 62.00 mm, IP66, IP68 - 2.5 bar, Brass, nickel-plated
Order No.	1083400000
Type	KDSU M75 BN O NI 1 G75S
GTIN (EAN)	4032248847402
Qty.	1 items
Delivery status	Discontinued
Available until	2023-07-30T00:00:00+02:00

KDSU M75 BN O NI 1 G75S

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals	IECEXSIR; SIRAATEX
Approvals	EAC; ATEX; IECEX
Approvals	



ROHS	Conform
------	---------

Dimensions and weights

Height	131 mm	Height (inches)	5.1575 inch
Length	131 mm	Length (inches)	5.1575 inch
Net weight	1980 g		

Temperatures

Operating temperature	-35 °C...90 °C
-----------------------	----------------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	3394d55b-7892-488f-8603-ea218c1d0691

Certificate numbers cable gland

Identification	ATEX: II 2G, Ex db IIC Gb, Ex eb IIC Gb, II 1D, Ex ta IIIC Da, IECEX: Ex db IIC Gb, Ex eb IIC Gb, Ex ta IIIC Da	Certificate no. cable gland (IECEX)	IECEX CML 19.0109X
Certificate No. (IECEX)	IECEXSIR05.0067X	Certificate No. (ATEX)	SIRA05ATEX1285X
Approval conditions	ATEX, IECEX		

General information

Outer cable diameter, max.	68 mm	Outer cable diameter, min.	60.2 mm
Inner cable diameter, max.	62.00 mm	Inner cable diameter, min.	52.10 mm
O-Ring	NBR	Protection degree with GWDR	IP66, IP68 - 2.5 bar
Armour, max.	2.5 mm	Armour, min.	0.1 mm
Operating temperature range, max.	90 °C	Operating temperature range, min.	-35 °C
Pitch of thread	1.5 mm	Halogen	Yes
AF size 1	90 mm	AF size 2	90 mm
Protection degree	IP66, IP68 - 2.5 bar	Cable gland	metric, nickel-plated brass
Basic material	Brass, nickel-plated	Seal insert	CR
Sealing	CR	External thread	M 75
Length of thread	19 mm	Water depth	25 m (30 Min.)
Type of armouring, short term	SWA, STA, SWB	Type of armouring	Single-wire armouring, Metal foil armouring, Braided armouring
Installation guidelines	See assembly instructions	Size of protective cap	EL90

KDSU M75 BN O NI 1 G75S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Classifications**

ETIM 8.0	EC000441	ETIM 9.0	EC000441
ETIM 10.0	EC000441	ECLASS 14.0	27-14-08-04
ECLASS 15.0	27-14-08-04		

KDSU M75 BN O NI 1 G75S
Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com
Accessories
Brass lock nuts, nickel-plated


In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	SKMU M75 MS	Version
Order No.	1737060000	SKMU MS (brass locknut), Locknut, M 75, 7 mm, Brass, nickel-plated
GTIN (EAN)	4008190956530	
Qty.	5 ST	

Earth tags


In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	EA-RING MS/M 75	Version
Order No.	1736550000	EA (earthing rings), Earthing ring, Miscellaneous, M 75, Brass, nickel-plated
GTIN (EAN)	4008190963668	
Qty.	10 ST	

Vulcanised fibre gasket - KSWF


In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	KSWF M75	Version
Order No.	1076740000	KSWF (flat gasket - vulcanised fibre), Sealing ring, M 75, Vulcanized fibre
GTIN (EAN)	4032248838660	
Qty.	25 ST	

KDSU M75 BN O NI 1 G75S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories**Nylon flat gasket - KSWN**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	KSWN M75	Version
Order No.	1076670000	KSWN (flat gasket - nylon), Sealing ring, M 75, Nylon 6
GTIN (EAN)	4032248838714	
Qty.	25 ST	

Protective caps

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	KSP EL90	Version
Order No.	1076790000	KSP (Klippon shroud), Protective cap, PVC
GTIN (EAN)	4032248838608	
Qty.	10 ST	