

IE-PIC-HYB-S-0,5-300

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Hybrid, 10-pole. Inserts for plug-in connectors Variant 14

General ordering data

Version	Crimp contact, for plug insert, Hybrid
Order No.	1096180000
Type	IE-PIC-HYB-S-0,5-300
GTIN (EAN)	4032248869152
Qty.	300 items

IE-PIC-HYB-S-0,5-300

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Net weight	0.27 g
------------	--------

Temperatures

Storage temperature	Operating temperature
Installation temperature	

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Wire cross-section, finely stranded, max. AWG 20 (AWG)	Wire cross-section, finely stranded, min. AWG 24 (AWG)
Shielding	unshielded
Wire connection cross section, finely stranded, max.	0.5 mm ²
Connection 2	Crimp
Category	Miscellaneous
Wire connection cross section, finely stranded, min.	0.2 mm ²

Electrical properties

Nominal voltage	24 V
-----------------	------


Important note

Product information	Hybrid, 10-pole. Inserts for plug-in connectors Variant 14
---------------------	--

Classifications

ETIM 8.0	EC001121	ETIM 9.0	EC001121
ETIM 10.0	EC001121	ECLASS 14.0	27-44-03-90
ECLASS 15.0	27-44-03-90		

Dimensioned drawing



IE-PIC-HYB-S-0,5-300

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Crimping tools



Crimping tools for Weidmüller contacts for RSV and DSTV-HD systems

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation
- With end stop for exact positioning of the contacts

General ordering data

Type	HTF HYB	Version	
Order No.	1119580000	Pressing tool, Crimping tool for contacts, 0.08mm ² , 1mm ² ,	
GTIN (EAN)	4032248900626	FoderBcrimp	
Qty.	1 ST		