

**IE-KSF-PKV14M-KLROB-10M**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



Assembled IE cables

**General ordering data**

Order No.	1103660100
Type	<a href="#">IE-KSF-PKV14M-KLROB-10M</a>
GTIN (EAN)	4032248918409
Qty.	1 items

## IE-KSF-PKV14M-KLROB-10M

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Net weight	1287 g
------------	--------

### Temperatures

Storage temperature	Operating temperature	-40 °C...70
Installation temperature		

### Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1

### Electrical properties

Operating voltage	30
-------------------	----

### General standards

Connector standard	IEC 61076-3-119 CDV, IEC 61076-3-117 Var. 14
--------------------	--

### Standards

Connector standard	IEC 61076-3-119 CDV, IEC 61076-3-117 Var. 14
--------------------	--

### Cable structure

Sheathing colour	black (similar to RAL 9005)	Sheath diameter, max.	9.3 mm
------------------	-----------------------------	-----------------------	--------

### Electrical properties of cable

Operating voltage	30
-------------------	----

### Mechanical and material properties of cable

Min. bending radius, repetitive	10 x cable diameter	Min. bending radius, once only	5 x cable diameter
---------------------------------	---------------------	--------------------------------	--------------------

### Classifications

ETIM 8.0	EC001579	ETIM 9.0	EC001579
ETIM 10.0	EC001579	ECLASS 14.0	27-06-05-01
ECLASS 15.0	27-06-05-01		

