

IE-KSF-PKV14M-KLROB-20M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Assembled IE cables

General ordering data

Order No.	1103660200
Type	IE-KSF-PKV14M-KLROB-20M
GTIN (EAN)	4032248918737
Qty.	1 items

IE-KSF-PKV14M-KLROB-20M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Net weight	2396 g
------------	--------

Temperatures

Storage temperature	Operating temperature	-40 °C...70
Installation temperature		

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1

Electrical properties

Operating voltage	30
-------------------	----

General standards

Connector standard	IEC 61076-3-119 CDV, IEC 61076-3-117 Var. 14
--------------------	--

Standards

Connector standard	IEC 61076-3-119 CDV, IEC 61076-3-117 Var. 14
--------------------	--

Cable structure

Sheathing colour	black (similar to RAL 9005)	Sheath diameter, max.	9.3 mm
------------------	-----------------------------	-----------------------	--------

Electrical properties of cable

Operating voltage	30
-------------------	----

Mechanical and material properties of cable

Min. bending radius, repetitive	10 x cable diameter	Min. bending radius, once only	5 x cable diameter
---------------------------------	---------------------	--------------------------------	--------------------

Classifications

ETIM 8.0	EC001579	ETIM 9.0	EC001579
ETIM 10.0	EC001579	ECLASS 14.0	27-06-05-01
ECLASS 15.0	27-06-05-01		

IE-KSF-PKV14M-KLROB-20M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

