

THM WO VIN 25.4/36.5 WS IW

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

General ordering data

Version	THM, Conductor and cable markers, 4 - 7.5 mm, 25.4 x 36.5 mm, white
Order No.	111060000
Type	THM WO VIN 25.4/36.5 WS IW
GTIN (EAN)	403224888596 1
Qty.	1 ROL

THM WO VIN 25.4/36.5 WS IW

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	0.07 mm	Depth (inches)	0.0026 inch
Height	25.4 mm	Height (inches)	1 inch
Width	36.5 mm	Width (inches)	1.437 inch
Net weight	260 g		

Temperatures

Operating temperature range -40...80 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

Adhesive	Polyacrylate adhesive		
Material colour according to resistance code	9		
Type of printing	neutral		
Version	Self-adhesive		
Width	36.5 mm		
UL 94 flammability rating	V-0		
Operating temperature range, max.	80 °C		
Operating temperature range, min.	-40 °C		
Colour	white		
Halogen	Yes		
Basic material	Vinyl film		
Printed characters	without		
Number of markers per packaging unit	Form of supply	Label reel	
Size of labelling field	12.7 x 25.4 mm		
Approval acc. to UL 969 compatible printer	Yes THM MULTIMARK , THM MULTIMARK PLUS		
Number of markers per combination	1 Label reel = Conductor and cable markers		
Operating temperature range	-40...80 °C		
Number per roll	2500		


Conductor and cable markers

Halogen	Yes	Conductor cross-section, max.	35 mm ²
Conductor cross-section, min.	0.75 mm ²	Conductor O.D., max.	7.5 mm
Conductor O.D., min.	4 mm	Conductor O.D.	4 - 7.5 mm
Cross-section for connected wire	0.75 - 35 mm ²		

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

Drawings



THM WO VIN 25.4/36.5 WS IW

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Ink ribbons



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	RIBBON MM 110/360 SW	Version	
Order No.	2005070000	Ink ribbon	
GTIN (EAN)	4050118390049		
Qty.	1 ST		