

## THM WO VIN 25.4/95.2 WS IW

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

### General ordering data

Version	THM, Conductor and cable markers, 8.1 - 22.3 mm, 25.4 x 95.2 mm, white
Order No.	<a href="#">1110610000</a>
Type	THM WO VIN 25.4/95.2 WS IW
GTIN (EAN)	4032248885978
Qty.	1 ROL

**THM WO VIN 25.4/95.2 WS IW**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth	0.07 mm	Depth (inches)	0.0026 inch
Height	25.4 mm	Height (inches)	1 inch
Width	95.2 mm	Width (inches)	3.748 inch
Net weight	557 g		

**Temperatures**

Operating temperature range -40...80 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**General data**

Adhesive	Polyacrylate adhesive		
Material colour according to resistance code	9		
Type of printing	neutral		
Version	Self-adhesive		
Width	95.2 mm		
UL 94 flammability rating	V-0		
Operating temperature range, max.	80 °C		
Operating temperature range, min.	-40 °C		
Colour	white		
Halogen	Yes		
Basic material	Vinyl film		
Printed characters	without		
Number of markers per packaging unit	Form of supply	Label reel	
Size of labelling field	25.4 x 25.4 mm		
Approval acc. to UL 969 compatible printer	Yes <a href="#">THM MULTIMARK</a> , <a href="#">THM MULTIMARK PLUS</a>		
Number of markers per combination	1 Label reel = Conductor and cable markers		
Operating temperature range	-40...80 °C		
Number per roll	1000		


**Conductor and cable markers**

Halogen	Yes	Conductor cross-section, max.	400 mm <sup>2</sup>
Conductor cross-section, min.	0.75 mm <sup>2</sup>	Conductor O.D., max.	22.3 mm
Conductor O.D., min.	8.1 mm	Conductor O.D.	8.1 - 22.3 mm
Cross-section for connected wire	0.75 - 400 mm <sup>2</sup>		

**Classifications**

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

**Drawings**



## THM WO VIN 25.4/95.2 WS IW

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

# Accessories

## Ink ribbons



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

## General ordering data

Type	RIBBON MM 110/360 SW	Version	
Order No.	<a href="#">2005070000</a>	Ink ribbon	
GTIN (EAN)	4050118390049		
Qty.	1 ST		