

PS_ZQV**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

General ordering data

Version	Test adapter (terminal), 1000 V, 20 A
Order No.	1121740000
Type	PS_ZQV
GTIN (EAN)	4032248902675
Qty.	1 items

PS_ZQV

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Height	94 mm	Height (inches)	3.7008 inch
Diameter	4 mm	Net weight	14 g

Temperatures

Ambient temperature	-5 °C...40 °C
---------------------	---------------

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1
SCIP	8d191f1d-272c-40a1-8319-7de6fe5d9746

Material data

Colour	red
--------	-----

System specifications

Version	Test plug
---------	-----------

Additional technical data

With snap-in pegs	No	Type of mounting	Plugged
-------------------	----	------------------	---------

Conductors for clamping (rated connection)

Stripping length	20 mm	Type of connection	Plug-in connection
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max.	1.5 mm ²	Wire connection cross section, finely stranded, max.	1.5 mm ²
Connection cross-section, stranded, max.	1.5 mm ²		

Dimensions

Diameter	4 mm	Pitch in mm (P)	5.40 mm
----------	------	-----------------	---------

General

Number of poles	1
-----------------	---

Rating data

Rated voltage	1000 V	Max. voltage of clamp support & pluggable system	1000 V
Nominal current	20 A	Current at maximum wires	20 A

Technical data

Classifications

ETIM 8.0	EC002555	ETIM 9.0	EC002555
ETIM 10.0	EC002555	ECLASS 14.0	27-25-03-04
ECLASS 15.0	27-25-03-04		