



### General ordering data

Version	Cross-connector (terminal), when screwed in, grey, Number of poles: 10, Pitch in mm (P): 5.50, Insu- lated: No, Width: 6 mm
Order No.	<a href="#">1129300000</a>
Type	SAKQ 2.5/10
GTIN (EAN)	4032248996155
Qty.	20 items
Local product	Only available in certain countries

## SAKQ 2.5/10

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### General ordering data

Local product	Only available in certain countries
---------------	-------------------------------------

### Dimensions and weights

Depth	13.5 mm	Depth (inches)	0.5315 inch
Height	54 mm	Height (inches)	2.126 inch
Width	6 mm	Width (inches)	0.2362 inch
Net weight	10.52 g		

### Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
---------------------	----------------	---------------------	---------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### Material data

Colour	grey
--------	------

### System specifications

PE connection	No
---------------	----

### Additional technical data

Type of fixing	when screwed in	Explosion-tested version	No
----------------	-----------------	--------------------------	----

### Dimensions

Pitch in mm (P)	5.50 mm
-----------------	---------

### General

Number of poles	10
-----------------	----

### Rating data

Rated voltage	400 V
---------------	-------

### Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		