



General ordering data

Version	Cross-connector (terminal), when screwed in, grey, Number of poles: 3, Pitch in mm (P): 10.00, Insulated: No, Width: 6 mm
Order No.	1129410000
Type	SAKQ 10/3
GTIN (EAN)	4032248996261
Qty.	50 items
Local product	Only available in certain countries

Technical data

Approvals

ROHS	Conform
------	---------

General ordering data

Local product	Only available in certain countries
---------------	-------------------------------------

Dimensions and weights

Depth	15 mm	Depth (inches)	0.5906 inch
Height	28 mm	Height (inches)	1.1024 inch
Width	6 mm	Width (inches)	0.2362 inch
Net weight	6.53 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
---------------------	----------------	---------------------	---------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Colour	grey
--------	------

System specifications

PE connection	No
---------------	----

Additional technical data

Type of fixing	when screwed in	Explosion-tested version	No
----------------	-----------------	--------------------------	----

Dimensions

Pitch in mm (P)	10.00 mm
-----------------	----------

General

Number of poles	3
-----------------	---

Rating data

Rated voltage	400 V
---------------	-------

Classifications

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		