

## SAKEW 35

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



### General ordering data

Version	End and partition plate for terminals, grey, Height: 50 mm, Width: 8.5 mm, V-O, PA 66/6
Order No.	<a href="#">1129450000</a>
Type	SAKEW 35
GTIN (EAN)	4032248970612
Qty.	50 items

**SAKEW 35**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth including DIN rail	31.5 mm	Height	50 mm
Height (inches)	1.9685 inch	Width	8.5 mm
Width (inches)	0.3346 inch	Net weight	5.56 g

**Temperatures**

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
---------------------	----------------	---------------------	---------------

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Material data**

Basic material	PA 66/6	Colour	grey
UL 94 flammability rating	V-0		

**System specifications**

Version	End bracket	End cover plate required	No
PE connection	No	Mounting rail	TS 35

**Additional technical data**

Locking for screw fixing

**General**

Mounting rail TS 35

**Classifications**

ETIM 8.0	EC000886	ETIM 9.0	EC000886
ETIM 10.0	EC000886	ECLASS 14.0	27-25-03-01
ECLASS 15.0	27-25-03-01		