

**IE-BI-USB-AB**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



USB inserts for FrontCom®

**General ordering data**

Version	USB insert, Flange insert, type AB
Order No.	<a href="#">1131380000</a>
Type	IE-BI-USB-AB
GTIN (EAN)	4032248911844
Qty.	1 items

## Technical data

### Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E471884

### Dimensions and weights

Net weight 12.3 g

### Temperatures

Storage temperature	Operating temperature	-40 °C...70 °C
Installation temperature	Humidity	0...93 % rel. humidity

### Environmental Product Compliance

RoHS Compliance Status Compliant without exemption

REACH SVHC No SVHC above 0.1 wt%

### General data

Product type	USB insert	Protection degree	IP67 with housing
Insert type	Insert data SteadyTec		

### General Info

Connection 1	USB A	Connection 2	USB B
Description of article	Flange insert, type AB	Wiring	Typ A-B
Colour	black	Humidity	0...93 % rel. humidity
Housing main material	PC UL 94 V0	Shielding	360°; all-round enclosure
Protection degree	IP67 with housing	Plugging cycles	≥ 1500

### Electrical properties

Contact resistance	≤ 30 mΩ	Dielectric strength, contact / shield	≥ 500 V DC
Insulation resistance	≥ 1000 MΩ	Current-carrying capacity up to 90 °C	3 A

### General standards

Certificate No. (DNV)	TAA000022B	Connector standard	IEC 61076-3-107
Certificate no. (cULus)	E471884		

### Important note

Product information USB inserts for FrontCom®

### Classifications

ETIM 8.0	EC001121	ETIM 9.0	EC001121
ETIM 10.0	EC001121	ECLASS 14.0	27-44-03-90
ECLASS 15.0	27-44-03-90		

**Drawings**

**Dimensioned drawing**

