

## IE-BIC-HYB-P-0,2-300

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Hybrid, 10-pole. Inserts for plug-in connectors Variant 14

### General ordering data

Version	Crimp contact, for flange insert, Hybrid
Order No.	<a href="#">1135160000</a>
Type	IE-BIC-HYB-P-0,2-300
GTIN (EAN)	40322489 15477
Qty.	300 items

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Net weight 0.29 g

**Temperatures**

Storage temperature Installation temperature Operating temperature

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**General data**

Shielding	unshielded	Category	Miscellaneous
Wire connection cross section, finely stranded, max.	0.2 mm <sup>2</sup>	Wire connection cross section, finely stranded, min.	0.08 mm <sup>2</sup>
Connection 2	Crimp		

**Electrical properties**

Nominal voltage 24 V

**Important note**

Product information Hybrid, 10-pole. Inserts for plug-in connectors Variant 14

**Classifications**

ETIM 8.0	EC001121	ETIM 9.0	EC001121
ETIM 10.0	EC001121	ECLASS 14.0	27-44-03-90
ECLASS 15.0	27-44-03-90		

**Dimensioned drawing**

