

KDSX M63 BS O SC 1 G63
Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com
Similar to illustration


The KDSX features a special ring in the shape of a truncated cone. The braided armouring on the ring makes a connection between the cables and lines possible. The armour ensures a conductive connection between the cable and the cable gland. In addition, the KDSX comes with two seals which provide sealing for the outer and inner parts of the cable insulation. The cable armouring is located between the inner and outer insulation. The cable gland is equipped with a silicone seal for temperatures ranging from -60°C to +180°C. This sealing material allows you to achieve IP66 or IP67 protection. The KDSX is permitted for use with pressure-resistant Ex d encapsulations and increased safety Ex e.

General ordering data

Version	KDSX (Klippon double sealing SWB/STA Ex cable gland), Cable glands, straight, M 63, 19 mm, Braided armouring, 0.5 - 0.8 mm, OD min. 53.8 - OD max. 61.2 mm, ID min. 49.50 - ID max. 56.00 mm, IP66, IP68 - 2.5 bar, Brass
Order No.	1135840000
Type	KDSX M63 BS O SC 1 G63
GTIN (EAN)	4032248968305
Qty.	1 items
Delivery status	Discontinued
Available until	2023-07-30T00:00:00+02:00
Alternative product	E1XZ/63/M63-WM

Creation date 24.02.2026 07:41:25 MEZ

Catalogue status / Drawings

KDSX M63 BS 0 SC 1 G63

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals	IECEXSIR; SIRAATEX
Approvals	EAC; ATEX; IECEX
Approvals	



ROHS	Conform
------	---------

Dimensions and weights

Height	76 mm	Height (inches)	2.9921 inch
Length	76 mm	Length (inches)	2.9921 inch
Net weight	1140 g		

Temperatures

Operating temperature	-60 °C...180 °C
-----------------------	-----------------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	3394d55b-7892-488f-8603-ea218c1d0691

Certificate numbers cable gland

Identification	ATEX: II 2G, Ex db IIC Gb, Ex eb IIC Gb, II 1D, Ex ta IIIC Da, IECEX: Ex db IIC Gb, Ex eb IIC Gb, Ex ta IIIC Da	Certificate no. cable gland (IECEX)	IECEX CML 19.0109X
Certificate No. (IECEX)	IECEXSIR05.0067X	Certificate No. (ATEX)	SIRA05ATEX1286X
Approval conditions	ATEX, IECEX		

General information

Outer cable diameter, max.	61.2 mm	Outer cable diameter, min.	53.8 mm
Inner cable diameter, max.	56.00 mm	Inner cable diameter, min.	49.50 mm
Protection degree with GWDR	IP66, IP68 - 2.5 bar	Armour, max.	0.8 mm
Armour, min.	0.5 mm	Operating temperature range, max.	180 °C
Operating temperature range, min.	-60 °C	Pitch of thread	1.5 mm
Halogen	No	AF size 1	80 mm
AF size 2	80 mm	Protection degree	IP54
Cable gland	metric, brass	Basic material	Brass
Seal insert	Silicone	Sealing	Silicone
External thread	M 63	Length of thread	19 mm
Water depth	25 m (30 Min.)	Type of armouring, short term	SWB
Explosion protection type	Improved safety Ex e, Pressure-resistant Ex d encapsulation	Type of armouring	Braided armouring
Installation guidelines	See assembly instructions	Size of protective cap	L80

KDSX M63 BS 0 SC 1 G63**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Classifications**

ETIM 8.0	EC000441	ETIM 9.0	EC000441
ETIM 10.0	EC000441	ECLASS 14.0	27-14-08-04
ECLASS 15.0	27-14-08-04		

KDSX M63 BS O SC 1 G63

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Brass lock nuts, natural finish



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	SKMU M63 MS SC	Version
Order No.	0930640007	SKMU MS (brass locknut), Locknut, M 63, 6.4 mm, Brass
GTIN (EAN)	4032248976119	
Qty.	5 ST	

Safety serrated washer



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	SZS M63	Version
Order No.	1736360000	SZS (serrated washer), Retaining toothed washers, M 63, Stainless steel 1.4404 (316L)
GTIN (EAN)	4008190963569	
Qty.	5 ST	

Earth tags



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	EA-RING MS/M 63	Version
Order No.	1736540000	EA (earthing rings), Earthing ring, Miscellaneous, M 63, Brass, nickel-plated
GTIN (EAN)	4008190963651	
Qty.	10 ST	

KDSX M63 BS 0 SC 1 G63

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories**Nylon flat gasket - KSWN**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	KSWN M63	Version
Order No.	1076660000	KSWN (flat gasket - nylon), Sealing ring, M 63, Nylon 6
GTIN (EAN)	4032248838707	
Qty.	25 ST	

Protective caps

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	KSP L80	Version
Order No.	1736630000	KSP (Klippon shroud), Protective cap, PVC
GTIN (EAN)	4008190956295	
Qty.	10 ST	

Type	KSP L80 S	Version
Order No.	0930700007	KSP (Klippon shroud), Protective cap, Silicone
GTIN (EAN)	4032248976027	
Qty.	10 ST	