

**VKSW****Weidmüller Interface GmbH & Co. KG**Klingenbergsstraße 26  
D-32758 Detmold  
Germany[www.weidmueller.com](http://www.weidmueller.com)

Wire channel cutter for manual operation in cutting wiring channels and covers up to 125 mm wide and a wall thickness of 2.5 mm. Only for plastics not reinforced by fillers.

- Cutting with no burrs or waste
- Length stop (1,000 mm) with guide device for precise cutting to length
- Table-top unit for mounting on a workbench or similar work surface
- Hardened cutting edges made of special steel

**General ordering data**

Version	Cable duct cutting device
Order No.	<a href="#">1137530000</a>
Type	VKSW
GTIN (EAN)	4032248919406
Qty.	1 items

**Technical data****Dimensions and weights**

Depth	290 mm
Height	285 mm
Width	280 mm
Net weight	305 g

Depth (inches)	11.4173 inch
Height (inches)	11.2204 inch
Width (inches)	11.0236 inch

**Environmental Product Compliance**

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

**Cutting tools**

Cutting width max.	125 mm
--------------------	--------

**Classifications**

ETIM 8.0	EC002691
ETIM 10.0	EC002691
ECLASS 15.0	21-04-50-03

ETIM 9.0	EC002691
ECLASS 14.0	21-04-50-03

## Accessories

## Accessories / replacement parts



Wire channel cutter for manual operation in cutting wiring channels and covers up to 125 mm wide and a wall thickness of 2.5 mm. Only for plastics not reinforced by fillers.

- Cutting with no burrs or waste
- Length stop (1,000 mm) with guide device for precise cutting to length
- Table-top unit for mounting on a workbench or similar work surface
- Hardened cutting edges made of special steel

## General ordering data

Type	ERME VKSW	Version
Order No.	<a href="#">1251270000</a>	Spare cutting blade
GTIN (EAN)	4050118042436	
Qty.	1 ST	
Type	SCHUTZPROFIL VKSW	Version
Order No.	<a href="#">2007400000</a>	
GTIN (EAN)	4050118392548	
Qty.	1 ST	
Type	VKSW HANDLE	Version
Order No.	<a href="#">2886200000</a>	
GTIN (EAN)	4064675855200	
Qty.	1 ST	