

VKSW**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Wire channel cutter for manual operation in cutting wiring channels and covers up to 125 mm wide and a wall thickness of 2.5 mm. Only for plastics not reinforced by fillers.

- Cutting with no burrs or waste
- Length stop (1,000 mm) with guide device for precise cutting to length
- Table-top unit for mounting on a workbench or similar work surface
- Hardened cutting edges made of special steel

General ordering data

Version	Cable duct cutting device
Order No.	1137530000
Type	VKSW
GTIN (EAN)	4032248919406
Qty.	1 items

VKSW

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	290 mm	Depth (inches)	11.4173 inch
Height	285 mm	Height (inches)	11.2204 inch
Width	280 mm	Width (inches)	11.0236 inch
Net weight	305 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

Cutting tools

Cutting width max.	125 mm
--------------------	--------

Classifications

ETIM 8.0	EC002691	ETIM 9.0	EC002691
ETIM 10.0	EC002691	ECLASS 14.0	21-04-50-03
ECLASS 15.0	21-04-50-03		

Accessories

Accessories / replacement parts



Wire channel cutter for manual operation in cutting wiring channels and covers up to 125 mm wide and a wall thickness of 2.5 mm. Only for plastics not reinforced by fillers.

- Cutting with no burrs or waste
- Length stop (1,000 mm) with guide device for precise cutting to length
- Table-top unit for mounting on a workbench or similar work surface
- Hardened cutting edges made of special steel

General ordering data

Type	ERME VKSW	Version
Order No.	1251270000	Spare cutting blade
GTIN (EAN)	4050118042436	
Qty.	1 ST	
Type	SCHUTZPROFIL VKSW	Version
Order No.	2007400000	
GTIN (EAN)	4050118392548	
Qty.	1 ST	
Type	VKSW HANDLE	Version
Order No.	2886200000	
GTIN (EAN)	4064675855200	
Qty.	1 ST	