

WAD WMF2.5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image



The comprehensive accessories of the Klippon® Connect portfolio are perfectly matched down to the last detail. This facilitates mounting while adhering to required norms

General ordering data

Version	Terminal cover, dark beige, Wemid, Height: 11 mm, Width: 9.96 mm, Depth: 9.68 mm, V-0
Order No.	1142970000
Type	WAD WMF2.5
GTIN (EAN)	4032248926039
Qty.	50 items

WAD WMF2.5

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	9.68 mm	Depth (inches)	0.3811 inch
Height	11 mm	Height (inches)	0.4331 inch
Width	9.96 mm	Width (inches)	0.3921 inch
Net weight	0.53 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-50 °C...75 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	Wemid	Colour	dark beige
UL 94 flammability rating	V-0		

System specifications

Version	For the terminals
---------	-------------------

General

Number of poles	2
-----------------	---

Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		