

AP WMF2.5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image



The comprehensive accessories of the Klippon® Connect portfolio are perfectly matched down to the last detail. This facilitates mounting while adhering to required norms

General ordering data

| | |
|------------|---|
| Version | End plate for terminals, beige, Height: 87.25 mm, Width: 1.5 mm, V-0, Wemid, Snap-on: Yes |
| Order No. | 1142990000 |
| Type | AP WMF2.5 |
| GTIN (EAN) | 4032248925889 |
| Qty. | 50 items |

AP WMF2.5

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|----------|-----------------|-------------|
| Depth | 44.25 mm | Depth (inches) | 1.7421 inch |
| Height | 87.25 mm | Height (inches) | 3.435 inch |
| Width | 1.5 mm | Width (inches) | 0.0591 inch |
| Net weight | 5.07 g | | |

Temperatures

| | | | |
|----------------------------------|----------------|----------------------------------|----------------|
| Storage temperature | -25 °C...55 °C | Ambient temperature | -50 °C...75 °C |
| Continuous operating temp., min. | -50 °C | Continuous operating temp., max. | 120 °C |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Material data

| | | | |
|---------------------------|-------|--------|-------|
| Basic material | Wemid | Colour | beige |
| UL 94 flammability rating | V-0 | | |

System specifications

| | |
|---------|-----------|
| Version | End plate |
|---------|-----------|

Additional technical data

| | | | |
|---------|-----|---------------------|-----------------|
| Snap-on | Yes | Installation advice | Direct mounting |
|---------|-----|---------------------|-----------------|

General

| | |
|---------------------|-----------------|
| Installation advice | Direct mounting |
|---------------------|-----------------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000886 | ETIM 9.0 | EC000886 |
| ETIM 10.0 | EC000886 | ECLASS 14.0 | 27-25-03-01 |
| ECLASS 15.0 | 27-25-03-01 | | |