

ACT20X-CJC-HTI-S PRT 21

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Similar to illustration**General ordering data**

Version	(CJC) cold-junction compensation terminal for ACT20X thermal module, built-in PT100 sensor, Labelling for channel 2 (21, 22, 23, 24)
Order No.	1160650000
Type	ACT20X-CJC-HTI-S PRT 21
GTIN (EAN)	4032248948352
Qty.	1 items

ACT20X-CJC-HTI-S PRT 21

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	30.6 mm	Depth (inches)	1.2047 inch
Height	29 mm	Height (inches)	1.1417 inch
Width	14.6 mm	Width (inches)	0.5748 inch
Net weight	8.2 g		

Temperatures

Storage temperature	Operating temperature	-20 °C...70 °C
---------------------	-----------------------	----------------

Probability of failure

SIL in compliance with IEC 61508	None
----------------------------------	------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	7a, 7cl
REACH SVHC	Lead 7439-92-1
SCIP	2f6dd957-421a-46db-a0c2-cf1609156924

Connection data

Type of connection	Screw connection	Tightening torque, min.	0.4 Nm
Tightening torque, max.	0.6 Nm	Clamping range, rated connection	2.5 mm ²
Clamping range, min.	0.5 mm ²	Clamping range, max.	2.5 mm ²
Wire connection cross section AWG, min.	AWG 30	Wire connection cross section AWG, max.	AWG 14
Pitch in mm (P)	5.00 mm		

Classifications

ETIM 8.0	EC002637	ETIM 9.0	EC002637
ETIM 10.0	EC002637	ECLASS 14.0	27-20-02-92
ECLASS 15.0	27-20-02-92		

ACT20X-CJC-HTI-S PRT 21

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

