

AP MCZ1.5 GN 1670

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image

Similar to illustration

Open miniature housing in modular terminal format with five tension clamp connections. A transparent hinged top plate can be used for labelling and provides access to potentiometer and status displays. Plug-in cross-connectors can be used to interconnect the three top connections. A cover plate for closing off the housing is also available.

General ordering data

Version	End plate, OMNIMATE Housing - TERMINALBOX green, End plate, Width: 1.5 mm
Order No.	1161290000
Type	AP MCZ1.5 GN 1670
GTIN (EAN)	4032248950355
Qty.	50 items

AP MCZ1.5 GN 1670

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	55.85 mm	Depth (inches)	2.1988 inch
Height	91 mm	Height (inches)	3.5827 inch
Width	1.5 mm	Width (inches)	0.0591 inch
Length	0 mm	Net weight	5.97 g

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

UL 94 flammability rating	V-0	Insulating material	PA 66/6
Insulating material group	I	Surface finish	untreated
Basic material	PA 66/6	Comparative Tracking Index (CTI)	600 ≤ CTI

General data

Colour	green	Protection degree	IP20 in installed state
Mounting rail	TS 35	Colour chart (similar)	RAL 6032
Encapsulation option	Yes		

Assembly properties

Number of poles	5
-----------------	---

Housing properties

Number of poles	5
-----------------	---

Classifications

ETIM 8.0	EC000886	ETIM 9.0	EC001031
ETIM 10.0	EC001031	ECLASS 14.0	27-19-06-02
ECLASS 15.0	27-19-06-02		

Drawing

