

**IL WMF2.5 BLZ OR**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Product image**

The comprehensive accessories of the Klippon® Connect portfolio are perfectly matched down to the last detail. This facilitates mounting while adhering to required norms

**General ordering data**

Version	Locking clips (terminal), PA 66, orange
Order No.	<a href="#">1167440000</a>
Type	IL WMF2.5 BLZ OR
GTIN (EAN)	4032248958474
Qty.	50 items

**IL WMF2.5 BLZ OR**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS	Conform
------	---------

**Dimensions and weights**

Depth	28.85 mm	Depth (inches)	1.1358 inch
Height	16.6 mm	Height (inches)	0.6535 inch
Width	8.28 mm	Width (inches)	0.326 inch
Net weight	1.12 g		

**Temperatures**

Storage temperature	-25 °C...55 °C	Ambient temperature	-50 °C...55 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Material data**

Basic material	PA 66	Colour	orange
UL 94 flammability rating	V-2		

**General**

Number of poles	2
-----------------	---

**Classifications**

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		