

IL WMF2.5 BLZ OR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image

The comprehensive accessories of the Klippon® Connect portfolio are perfectly matched down to the last detail. This facilitates mounting while adhering to required norms

General ordering data

Version	Locking clips (terminal), PA 66, orange
Order No.	1167440000
Type	IL WMF2.5 BLZ OR
GTIN (EAN)	4032248958474
Qty.	50 items

IL WMF2.5 BLZ OR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	28.85 mm	Depth (inches)	1.1358 inch
Height	16.6 mm	Height (inches)	0.6535 inch
Width	8.28 mm	Width (inches)	0.326 inch
Net weight	1.12 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-50 °C...55 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	PA 66	Colour	orange
UL 94 flammability rating	V-2		

General

Number of poles 2

Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		