

FUCR 10-36V SW**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

The comprehensive accessories of the Klippon® Connect portfolio are perfectly matched down to the last detail. This facilitates mounting while adhering to required norms

General ordering data

Version	Fuse holder for feed-through modular terminal, black, 6.3 A, Pivoting, pluggable, V-O, Wemid
Order No.	1167640000
Type	FUCR 10-36V SW
GTIN (EAN)	4032248113972
Qty.	10 items

FUCR 10-36V SW

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	40.5 mm	Depth (inches)	1.5945 inch
Height	38 mm	Height (inches)	1.4961 inch
Width	8 mm	Width (inches)	0.315 inch
Net weight	6.58 g		

Temperatures

Ambient temperature	-5 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	120 °C		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	Wemid	Colour	black
UL 94 flammability rating	V-0		

System specifications

Version	Fuse cartridge
---------	----------------

Additional technical data

Installation advice	Direct mounting	Type of mounting	Plugged
---------------------	-----------------	------------------	---------

General

Installation advice	Direct mounting	Operating temperature range, max.	120 °C
---------------------	-----------------	-----------------------------------	--------

Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		