

**TW PRV16****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

The comprehensive accessories of the Klippon® Connect portfolio are perfectly matched down to the last detail. This facilitates mounting while adhering to required norms

**General ordering data**

Version	P-series, Partition plate, grey, 2 mm, Unprinted
Order No.	<a href="#">1173630000</a>
Type	TW PRV16
GTIN (EAN)	4032248966127
Qty.	10 items

**TW PRV16**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth	100 mm	Depth (inches)	3.937 inch
Height	225 mm	Height (inches)	8.8582 inch
Width	2 mm	Width (inches)	0.0787 inch
Net weight	26.59 g		

**Temperatures**

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	125 °C

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Material data**

Basic material	Polycarbonate	Colour	grey
UL 94 flammability rating	V-0		

**System specifications**

Version	Unprinted	Number of levels	16
---------	-----------	------------------	----

**Additional technical data**

Snap-on	Yes
---------	-----

**Classifications**

ETIM 8.0	EC000886	ETIM 9.0	EC000886
ETIM 10.0	EC000886	ECLASS 14.0	27-25-03-01
ECLASS 15.0	27-25-03-01		