

**SKMUS M16-W****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

Version	SKMU SS (stainless steel locknut), Locknut, M16, 2.2 mm, Stainless steel 1.4404
Order No.	<a href="#">1185680000</a>
Type	SKMUS M16-W
GTIN (EAN)	4050118269956
Qty.	240 items

**SKMUS M16-W**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Height	3.2 mm	Height (inches)	0.126 inch
Net weight	4 g		

**Temperatures**

Operating temperature

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**General information**

Pitch of thread	1.5 mm	Halogen	halogen-free
AF size 1	20 mm	Thickness	2.80 mm
Cable gland	M 16	Basic material	Stainless steel 1.4404
External thread	M16	Internal thread	M 16
Length of thread	2.2 mm		

**Classifications**

ETIM 8.0	EC000940	ETIM 9.0	EC000940
ETIM 10.0	EC000940	ECLASS 14.0	27-14-08-05
ECLASS 15.0	27-14-08-05		