

SKMUS M25-W**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	SKMU SS (stainless steel locknut), Locknut, M 25, 2.2 mm, Stainless steel 1.4404
Order No.	1185700000
Type	SKMUS M25-W
GTIN (EAN)	4050118269963
Qty.	240 items

SKMUS M25-W

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Height	3.2 mm	Height (inches)	0.126 inch
Net weight	7 g		

Temperatures

Operating temperature

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General information

Pitch of thread	1.5 mm	Halogen	halogen-free
AF size 1	30 mm	Thickness	3.00 mm
Cable gland	M 25	Basic material	Stainless steel 1.4404
External thread	M 25	Internal thread	M 25
Length of thread	2.2 mm		

Classifications

ETIM 8.0	EC000940	ETIM 9.0	EC000940
ETIM 10.0	EC000940	ECLASS 14.0	27-14-08-05
ECLASS 15.0	27-14-08-05		