

A2LCS/40/NPT1-1/4-M40F

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



A2LC type cable glands are suitable for un-armored cable and provide a conduit connection female thread, maintains flameproof Ex d and Increased Safety Ex e explosion protection.

General ordering data

Version	A2LC (Klippon unarmored with conduit connection thread, Ex e/d cable gland), Cable glands, straight, 1 1/4" NPT, 18 mm, OD min. 25.5 - OD max. 32.2 mm, Stainless steel 1.4404
Order No.	1187510000
Type	A2LCS/40/NPT1-1/4-M40F
GTIN (EAN)	4050118081428
Qty.	9 items
Delivery status	Discontinued
Available until	2024-08-31T00:00:00+02:00

A2LCS/40/NPT1-1/4-M40F

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Height	55.8 mm	Height (inches)	2.1968 inch
Width	55 mm	Width (inches)	2.1654 inch
Length	71.8 mm	Length (inches)	2.8268 inch
Net weight	414 g		

Temperatures

Operating temperature -50 °C... 120 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

Certificate numbers cable gland

Identification	II 2G 1D, Ex db IIC Gb, Ex eb IIC Gb, Ex ta IIIC Da	Certificate no. cable gland (ATEX)	TÜV IT 16ATEX 059X
Certificate no. cable gland (IECEX)	IECEX TPS 16.0004X	Certificate no. cable gland (CCC)	2020322313000069
Certificate No. (IECEX)	IECEXTPS16.0004X		

General information

Outer cable diameter, max.	32.2 mm	Outer cable diameter, min.	25.5 mm
O-Ring	Silicone	Tightening torque	80 Nm
Silicone	Yes	Operating temperature range, max.	120 °C
Operating temperature range, min.	-50 °C	Pitch of thread	2.21 mm
Halogen	No	Standards	EN 60079-0, EN 60079-1, EN 60079-31, EN 60079-7, GB 12476.1, GB 12476.5, GB 3836.1, GB 3836.2, GB 3836.3, IEC 60079-0, IEC 60079-1, IEC 60079-31, IEC 60079-7
AF size 1	50 mm	AF size 2	50 mm
Protection degree	IP66, IP68	Cable gland	NPT 1-1/4"
Basic material	Stainless steel 1.4404	Seal insert	Silicone
Sealing	Silicone	External thread	1 1/4" NPT
Length of thread	18 mm	Conduit thread size (metric)	M40
Explosion protection type	Ex d - flameproof, Ex e - increased safety	Installation guidelines	See assembly instructions

Classifications

ETIM 8.0	EC000441	ETIM 9.0	EC000441
ETIM 10.0	EC000441	ECLASS 14.0	27-14-08-04
ECLASS 15.0	27-14-08-04		