

**MULTI-STRIPAX PV****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



- For flexible and solid conductors with special insulating materials
- High-quality stripping for industrial applications (complies with aircraft industry requirements)
- Specially shaped blades enable stripping of special types of insulation and conductor configurations
- Stripping length adjustable via end stop
- Very versatile thanks to interchangeable stripping units
- Stripping results reproduced accurately over and over again
- No damage to the conductor
- A long-lasting, reliable tool thanks to its sturdy design
- Integrated cutting function

**General ordering data**

Version	Photovoltaics, Plug-in connector
Order No.	<a href="#">1190490000</a>
Type	MULTI-STRIPAX PV
GTIN (EAN)	4032248973262
Qty.	1 items

**MULTI-STRIPAX PV**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Dimensions and weights**

Depth	40 mm	Depth (inches)	1.5748 inch
Height	85 mm	Height (inches)	3.3464 inch
Width	250 mm	Width (inches)	9.8425 inch
Net weight	548 g		

**Environmental Product Compliance**

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

**Technical data**

Description of article	Wire stripper unit
------------------------	--------------------

**Stripping tools**

Cable type	Photovoltaic cables and similar earthing cables and short-circuit-proof cables	Conductor cross-section (cutting capacity)	16 mm <sup>2</sup>
Stripping range AWG, max.	8 AWG	Stripping range AWG, min.	14 AWG
Stripping length, min.	2 mm	Conductor cross-section, max.	10 mm <sup>2</sup>
Conductor cross-section, min.	4 mm <sup>2</sup>		

**Classifications**

ETIM 8.0	EC002109	ETIM 9.0	EC002109
ETIM 10.0	EC002109	ECLASS 14.0	21-04-37-06
ECLASS 15.0	21-04-37-06		