HDC 06B ADLU



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com









The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings -your first choice for industrial housings with IP 65 protection.

General ordering data

Version	HDC enclosures, Installation size: 3, Protection degree: IP65, in plugged condition, Bulkhead housing, End-locking clamp, lower side, End-locking clamp not replaceable, Standard, with cover
Order No.	<u>1202500000</u>
Туре	HDC 06B ADLU
GTIN (EAN)	4008190889920
Qty.	1 items



HDC 06B ADLU



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

Approvals

Approvals CE_{c} SU_{us}

ROHS	Conform
UL File Number Search	<u>UL Website</u>
Certificate No. (cURus)	E92202

Dimensions and weights

Height	47 mm	Height (inches)	1.8504 inch
Width	68 mm	Width (inches)	2.6772 inch
Mounting dimension - height	32 mm	Mounting dimension - width	70 mm
Net weight	159.28 g		

Temperatures

Limit temperature -40 °C ... 125 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption			
REACH SVHC	Potassium perfluorobutane sulfonat	Potassium perfluorobutane sulfonate 29420-49-3		
SCIP	e98b2b24-ba23-41bf-8d19-0dda3	e98b2b24-ba23-41bf-8d19-0dda3647412f		
Chemical resistance	Substance	Acetone		
	Chemical resistance	Conditionally resistant		
	Substance	Drilling oil		
	Chemical resistance	Resistant		
	Substance	Diesel		
	Chemical resistance	Resistant		
	Substance	Ethyl alcohol		
	Chemical resistance	Resistant		
	Substance	Transmission oil		
	Chemical resistance	Resistant		
	Substance	Hydraulic oil		
	Chemical resistance	Resistant		
	Substance	Coolant		
	Chemical resistance	Resistant		
	Substance	Petroleum benzine		
	Chemical resistance	Resistant		
	Substance	Sweat		
	Chemical resistance	Resistant		
	Substance	Premium gasoline		
	Chemical resistance	Conditionally resistant		
	Substance	Water		
	Chemical resistance	Resistant	Resistant	
	Substance	UV		
	Chemical resistance	Unstable		
	Substance	Ozone		
	Chemical resistance	Unstable		

Dimensions

Hole pitch length A2	70 mm	Width housing C	43 mm	
Width base C1	45 mm	Total length housing	60 mm	

Creation date 29.11.2025 06:57:02 MEZ

Catalogue status / Drawings 2



HDC 06B ADLU



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

Height of housing B	29 mm	Height of base B1	6 mm
General data			
Tightening torque	1.2 Nm	Housing main material	diecast aluminium
Surface finish	Powder coating	Protection degree	IP65, in plugged condition
Protection class note	Protection class with secured cover: IP 65	EMC housings	No No
Material of locking element	Stainless steel, rust-proof		
Version			
Top part/bottom part/lid	lower part	Cover	with cover
Tightening torque	1.2 Nm	Design of cover	with cover
Design of housing	Bulkhead housing	Design of locking system	End-locking clamp, lower side, End-locking clamp not replaceable
Design	Standard	Installation size	3
Туре	Bulkhead (feed-through)	Clamp version	End-locking clamp
Sealing	NBR	Colour (RAL)	RAL 7035
BG	3	Suitable for ModuPlug®	Yes
Important note			
Product information	When mounting the housir	ngs, make sure that the flat gasket is	correctly seated.
Classifications			
ETIM C O	FC000427	ETINA 7.0	FC000427
ETIM 6.0	EC000437	ETIM 7.0	EC000437
ETIM 8.0	EC000437 EC000437	ETIM 9.0	EC000437
ETIM 10.0		ECLASS 9.0	27-44-02-02
ECLASS 9.1	27-44-02-02	ECLASS 10.0	27-44-02-02
ECLASS 11.0	27-44-02-02	ECLASS 12.0	27-44-02-02
ECLASS 13.0	27-44-02-02	ECLASS 14.0	27-44-02-02
ECLASS 15.0	27-44-02-02		

Catalogue status / Drawings