Data sheet

SAI M23 CRIMPING TOOL 2

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Weidmüller offers a wide range of tools and accessories for sensor-actuator cabling.

General ordering data

Version	Pressing tool for signal contacts, 4-indent crimp
Order No.	1203960000
Type	SAI M23 CRIMPING TOOL 2
GTIN (EAN)	4050118000764
Qty.	1 items
Delivery status	This article will no longer be available in the future.
Last order date	2026-12-31T00:00:00+01:00

SAI M23 CRIMPING TOOL 2

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Dimensions and weights

Length	175 mm	Length (inches)	6.8898 inch
Net weight	478 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	7baf363e-d867-435e-844e-c01f32ebf146

Technical data

Version	Mechanical, without interchangeable inserts	Operating temperature, min.	-40 °C

Description of contact

Type of contact	Turned contacts	Conductor cross-section, max. AWG	AWG 13
Conductor cross-section, min. AWG	AWG 28		

tool data crimping

Wire end ferrules cross-section, max.	2.5 mm²	Wire end ferrules cross-section, min.	0.14 mm²
Crimping type/profile	4-indent crimp		

Classifications

ETIM 8.0	EC000168	ETIM 9.0	EC000168
ETIM 10.0	EC000168	ECLASS 14.0	21-04-38-11
ECLASS 15.0	21-04-38-11		