


ESG 9/17 K MC NE BL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Similar to illustration



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | |
|------------|---|
| Version | ESG, Device markers x 17 mm, PA 66, Colour: blue, Self-adhesive |
| Order No. | 1208960000 |
| Type | ESG 9/17 K MC NE BL |
| GTIN (EAN) | 403224899035 1 |
| Qty. | 200 items |

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 0.8 mm | Depth (inches) | 0.0315 inch |
| Height | 9 mm | Height (inches) | 0.3543 inch |
| Width | 17 mm | Width (inches) | 0.6693 inch |
| Net weight | 0.54 g | | |

Temperatures

| | |
|-----------------------------|-------------|
| Operating temperature range | -40...60 °C |
|-----------------------------|-------------|

Environmental Product Compliance

| | | | |
|--------------------------|-----------------------------|------------------|--|
| RoHS Compliance Status | Compliant without exemption | | |
| REACH SVHC | No SVHC above 0.1 wt% | | |
| Product Carbon Footprint | Cradle to gate | 0.003 kg CO2 eq. | |

General data

| | | | |
|--------------------------------------|---|-----------|--|
| Adhesive | Double-sided adhesive tape | | |
| Number per sheet | 40 | | |
| Version | Self-adhesive | | |
| Width | 17 mm | | |
| UL 94 flammability rating | V-2 | | |
| Operating temperature range, max. | 60 °C | | |
| Operating temperature range, min. | -40 °C | | |
| Colour | blue | | |
| Halogen | No | | |
| Basic material | PA 66 | | |
| Printed characters | without | | |
| Number of markers per packaging unit | Form of supply | MultiCard | |
| compatible printer | PRINTJET CONNECT , MCP BASIC 2 , MCP PLUS 2 | | |
| Number of markers per combination | 1 MultiCard = Device markers | | |
| Operating temperature range | -40...60 °C | | |
| Application/manufacturer | Self-adhesive | | |

Device markers

| | |
|---------|----|
| Halogen | No |
|---------|----|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001288 | ETIM 9.0 | EC001288 |
| ETIM 10.0 | EC001288 | ECLASS 14.0 | 27-28-11-04 |
| ECLASS 15.0 | 27-28-11-04 | | |

Drawings

