

VP-HEX M20-EX W**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



VP series stopping plugs provide a method of filling unused entries in Ex equipment while maintaining Flame-proof Ex d and Increased Safety Ex e explosion protection and IP66/67/68 ingress rate.

General ordering data

| | |
|------------|---|
| Version | VP-HEX (Klippon Ex blanking plug with hexagon head), Blanking plug, straight, M 20 x 1.5, 16 mm, Brass, nickel-plated |
| Order No. | 1218950000 |
| Type | VP-HEX M20-EX W |
| GTIN (EAN) | 4050118075571 |
| Qty. | 24 items |

VP-HEX M20-EX W

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

| | | | |
|----------------------|-------|----------------------|-------------|
| Height | 20 mm | Height (inches) | 0.7874 inch |
| Width | 30 mm | Width (inches) | 1.1811 inch |
| Length | 20 mm | Length (inches) | 0.7874 inch |
| Diameter | 20 mm | Wall thickness, min. | 0.5 mm |
| Wall thickness, max. | 15 mm | Net weight | 40.79 g |

Temperatures

Operating temperature -50 °C...120 °C

Environmental Product Compliance

| | |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6c |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 0c0edf9f-b35a-4d1f-b8f0-99d4b22ac203 |

Certificate numbers cable gland

| | | | |
|-------------------------------------|---|------------------------------------|--------------------|
| Identification | II 2G 1D, Ex db IIC Gb, Ex eb IIC Gb, Ex ta IIIC Da | Certificate no. cable gland (ATEX) | TÜV IT 16ATEX 059X |
| Certificate no. cable gland (IECEX) | IECEX TPS 16.0004X | Certificate no. cable gland (CCC) | 2020322313000069 |
| Certificate No. (IECEX) | IECEXTPS16.0004X | | |

General information

| | | | |
|---------------------------|--|--------------------------|---|
| O-Ring | Silicone | Tightening torque | 40 Nm |
| Silicone | Yes | Pitch of thread | 1.5 mm |
| Halogen | halogen-free | Standards | EN 60079-0, EN 60079-1, EN 60079-31, EN 60079-7, GB 12476.1, GB 12476.5, GB 3836.1, GB 3836.2, GB 3836.3, IEC 60079-0, IEC 60079-1, IEC 60079-31, IEC 60079-7 |
| Impact resistance | 7.00 J | AF size 1 | 27 mm |
| Protection degree | IP66, IP68 | Cable gland | M 20 |
| Basic material | Brass, nickel-plated | Diameter of sealing ring | 20.00 mm |
| External thread | M 20 x 1.5 | Length of thread | 16 mm |
| Explosion protection type | Ex d - flameproof, Ex e - increased safety | Installation guidelines | See assembly instructions |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000451 | ETIM 9.0 | EC000451 |
| ETIM 10.0 | EC000451 | ECLASS 14.0 | 27-14-08-05 |
| ECLASS 15.0 | 27-14-08-05 | | |

VP-HEX M20-EX W

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Nylon flat washer - GWDR



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

| | | | |
|------------|----------------------------|---------|--------------------------------|
| Type | GWDR M20-W | Version | |
| Order No. | 1185610000 | | in closed state, M 20, Nylon 6 |
| GTIN (EAN) | 4050118078305 | | |
| Qty. | 100 ST | | |

Brass lock nuts, nickel-plated



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

| | | | |
|------------|----------------------------|---------|--|
| Type | SKMU M20 MS | Version | |
| Order No. | 1737000000 | | SKMU MS (brass locknut), Locknut, M 20, 3 mm, Brass, nickel-plated |
| GTIN (EAN) | 4008190956479 | | |
| Qty. | 100 ST | | |