

**VP-HEX M25-EX W****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



VP series stopping plugs provide a method of filling unused entries in Ex equipment while maintaining Flame-proof Ex d and Increased Safety Ex e explosion protection and IP66/67/68 ingress rate.

**General ordering data**

Version	VP-HEX (Klippon Ex blanking plug with hexagon head), Blanking plug, straight, M 25 x 1.5, 16 mm, Brass, nickel-plated
Order No.	<a href="#">1218960000</a>
Type	VP-HEX M25-EX W
GTIN (EAN)	4050118075588
Qty.	16 items

## VP-HEX M25-EX W

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

## Dimensions and weights

Height	21 mm	Height (inches)	0.8268 inch
Width	36.5 mm	Width (inches)	1.437 inch
Length	21 mm	Length (inches)	0.8268 inch
Diameter	25 mm	Wall thickness, min.	0.5 mm
Wall thickness, max.	15 mm	Net weight	64 g

## Temperatures

Operating temperature -50 °C...120 °C

## Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	0c0edf9f-b35a-4d1f-b8f0-99d4b22ac203

## Certificate numbers cable gland

Identification	II 2G 1D, Ex db IIC Gb, Ex eb IIC Gb, Ex ta IIIC Da	Certificate no. cable gland (ATEX)	TÜV IT 16ATEX 059X
Certificate no. cable gland (IECEX)	IECEX TPS 16.0004X	Certificate no. cable gland (CCC)	2020322313000069
Certificate No. (IECEX)	IECEXTPS16.0004X		

## General information

O-Ring	Silicone	Tightening torque	55 Nm
Silicone	Yes	Pitch of thread	1.5 mm
Halogen	halogen-free	Standards	EN 60079-0, EN 60079-1, EN 60079-31, EN 60079-7, GB 12476.1, GB 12476.5, GB 3836.1, GB 3836.2, GB 3836.3, IEC 60079-0, IEC 60079-1, IEC 60079-31, IEC 60079-7
Impact resistance	7.00 J	AF size 1	33 mm
Protection degree	IP66, IP68	Cable gland	M 25
Basic material	Brass, nickel-plated	Diameter of sealing ring	25.00 mm
External thread	M 25 x 1.5	Length of thread	16 mm
Explosion protection type	Ex d - flameproof, Ex e - increased safety	Installation guidelines	See assembly instructions

## Classifications

ETIM 8.0	EC000451	ETIM 9.0	EC000451
ETIM 10.0	EC000451	ECLASS 14.0	27-14-08-05
ECLASS 15.0	27-14-08-05		

## VP-HEX M25-EX W

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

## Nylon flat washer - GWDR



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

## General ordering data

Type	GWDR M25-W	Version	
Order No.	<a href="#">1185620000</a>		in closed state, M 25, Nylon 6
GTIN (EAN)	4064675423263		
Qty.	100 ST		

## Brass lock nuts, nickel-plated



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

## General ordering data

Type	SKMU M25 MS	Version	
Order No.	<a href="#">1737010000</a>		SKMU MS (brass locknut), Locknut, M 25, 3.5 mm, Brass, nickel-plated
GTIN (EAN)	4008190956486		
Qty.	100 ST		