


HDC HP 550 F 25**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Crimps provide a electrical and mechanical connection between wire and contact that is both secure and reliable. The optimal crimp connection is gas-tight and corrosion-resistant.

General ordering data

Version	HDC insert, Female, Crimp connection, Installation size: 550
Order No.	1220570000
Type	HDC HP 550 F 25
GTIN (EAN)	4050118003840
Qty.	1 items
Delivery status	Discontinued
Available until	2025-09-30T00:00:00+02:00

HDC HP 550 F 25

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Length	98.3 mm	Length (inches)	3.8701 inch
Diameter	43 mm	Net weight	125 g

Temperatures

Limit temperature	-50 °C ... 120 °C
-------------------	-------------------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	6eabd5ae-2d6b-409e-8bdf-87c27ee10e40

General data

Plugging cycles, silver	≥ 500	Type of connection	Crimp connection
Installation size	550	UL 94 flammability rating	V-0
Volume resistance	≤0.1 mΩ	Colour	black
Insulation resistance	1010 Ω	Insulating material	Polyamide with fibre optic
Conductor cross-section	25 mm ²	Surface finish	Silver passivated
Plugging cycles	≥ 500	Type	Female
Pollution severity	PD 2 (PD 3)	Basic material	Copper alloy
Series	HighPower	Rated impulse voltage (DIN EN 61984)	15 kV
Operating voltage, max. (total temperature=60°C)	3000 V	Free from halogens	false
Rated current acc. to DIN EN 61984 (ambient temperature=20°C)	140 A	BG	550

Power contact

Type of connection, power contact	Crimp connection	Stripping length, performance contact	30 mm
Rated impulse voltage (DIN EN 61984), power contact	15 kV		

Version

Stripping length, rated connection	30 mm	Type of connection	Crimp connection
Installation size	550	Volume resistance	≤0.1 mΩ
Conductor cross-section, max.	25 mm ²	Conductor cross-section, min.	25 mm ²
Surface finish	Silver passivated	Basic material	Copper alloy
BG	550		

Important note


Product information	Depending on the intended operation, internally generated voltages can superimpose the working voltage and contain corresponding peaks. It is imperative to ensure that these peak voltages do not exceed the rated voltage. For applications outside of this specification, please contact us. The rated voltage of 3.6 kV must be reduced by 20% at operating temperatures above 100°C.
---------------------	---

Technical data

Classifications

ETIM 8.0	EC000796	ETIM 9.0	EC000796
ETIM 10.0	EC000796	ECLASS 14.0	27-44-02-04
ECLASS 15.0	27-44-02-04		

Drawings



HDC HP 550 F 25
Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com
Accessories
HighPower spare parts

General ordering data

Type	HDC HP CLAMP 550A	Version	
Order No.	2447780000	HDC-HighPower	
GTIN (EAN)	4050118461671		
Qty.	25 ST		

Tools


Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm²
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 2 Ah

General ordering data

Type	EPG 60	Version	
Order No.	2453810000	Pressing tools, Tools, Pressing tool, 6mm ² , 300mm ² , Hexagonal	
GTIN (EAN)	4050118468434	crimp, WM crimp, Indent crimp, Trapezoidal crimp, Oval crimping	
Qty.	1 ST		

HDC HP 550 F 25

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26


D-32758 Detmold

Germany

www.weidmueller.com

Accessories

... for compression cable lugs



Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm²
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 2 Ah

General ordering data

Type	ES EPG/HPG 60 HEX 25	Version
Order No.	2505180000	Crimping tool insert, 25mm ² , Hexagonal crimp
GTIN (EAN)	4050118519570	
Qty.	1 ST	

Tools



Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts

- extremely fast processing thanks to hydraulic support
- large processing range up to 400 mm²
- 360° revolving quick action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- Additional features for APG series:
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB

General ordering data

Type	APG 80	Version
Order No.	2853270000	6mm ² , 400mm ²
GTIN (EAN)	4064675477020	
Qty.	1 ST	

HDC HP 550 F 25**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****... for compression cable lugs (acc. to DIN 46235)**

Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts

- extremely fast processing thanks to hydraulic support
- large processing range up to 400 mm²
- 360° revolving quick action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- Additional features for APG series:
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB

General ordering data

Type	ES APG 80 HEX 25	Version
Order No.	1502640000	25mm ² , Hexagonal crimp
GTIN (EAN)	4050118310573	
Qty.	1 ST	