

**IE-BHD-V01M-SCA****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Bayonet plug-in connectors according to IEC  
61076-3-106 ver.1 (EtherNet/IP), metal, empty housing

**General ordering data**

Version	Empty enclosure, Flange-mounted housing, Variant 1 to IEC 61076-3-106, IP67
Order No.	<a href="#">1221030000</a>
Type	IE-BHD-V01M-SCA
GTIN (EAN)	4050118003956
Qty.	10 items

## IE-BHD-V01M-SCA

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E316369

### Dimensions and weights

Depth	27 mm	Depth (inches)	1.063 inch
Height	32 mm	Height (inches)	1.2598 inch
Width	32 mm	Width (inches)	1.2598 inch
Net weight	56.4 g		

### Temperatures

Storage temperature	Operating temperature	-40 °C...70 °C
Installation temperature		

### Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1, 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol 119-47-1
SCIP	e5bbf197-73b5-420b-90c0-0173b7b3b6b7

### General data

Colour	Miscellaneous	Housing main material	Zinc diecast
Type of mounting	4 screws, Central nut	Protection degree	IP67
Plugging cycles	750		

### General standards

Connector standard	IEC 61076-3-106 Var. 1	Certificate no. (cULus)	E316369
--------------------	------------------------	-------------------------	---------

### Classifications


ETIM 8.0	EC001031	ETIM 9.0	EC001031
ETIM 10.0	EC001031	ECLASS 14.0	27-19-01-04
ECLASS 15.0	27-19-01-04		

Installation cut-out



Mounting cut-out: 1. With central screw connection / 2. For mounting with four M3 screws

Detailed drawing



Wall thickness when using the central screw connection