

## HDC 32B TOBU 1M40G

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

### General ordering data

Version	HDC enclosures, Installation size: 10, Protection degree: IP65, in plugged condition, Plug housing, Cable entry from top, Side-locking clamp on lower side, Standard, Size of cable entries: M 40
Order No.	<a href="#">1221070000</a>
Type	HDC 32B TOBU 1M40G
GTIN (EAN)	4032248998180
Qty.	1 items

**HDC 32B TOBU 1M40G**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate No. (cURus)	E92202

**Dimensions and weights**

Depth	94 mm	Depth (inches)	3.7008 inch
Height	79 mm	Height (inches)	3.1102 inch
Width	98 mm	Width (inches)	3.8583 inch
Net weight	394 g		

**Temperatures**

Limit temperature	-40 °C ... 125 °C
-------------------	-------------------

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption	
REACH SVHC	No SVHC above 0.1 wt%	
Chemical resistance	Substance	Acetone
	Chemical resistance	Conditionally resistant
	Substance	Drilling oil
	Chemical resistance	Resistant
	Substance	Diesel
	Chemical resistance	Resistant
	Substance	Ethyl alcohol
	Chemical resistance	Resistant
	Substance	Transmission oil
	Chemical resistance	Resistant
	Substance	Hydraulic oil
	Chemical resistance	Resistant
	Substance	Coolant
	Chemical resistance	Resistant
	Substance	Petroleum benzine
	Chemical resistance	Resistant
	Substance	Sweat
	Chemical resistance	Resistant
	Substance	Premium gasoline
	Chemical resistance	Conditionally resistant
Substance	Water	
Chemical resistance	Resistant	
Substance	UV	
Chemical resistance	Unstable	
Substance	Ozone	
Chemical resistance	Unstable	

**Dimensions**

Cable entry	w. thread	Width housing C	82.5 mm
Total length housing	94 mm	Height of housing B	79 mm

**HDC 32B TOBU 1M40G**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**General data**

Surface finish	Powder coating	Protection degree	IP65, in plugged condition
----------------	----------------	-------------------	----------------------------

**Version**

Number of cable glands	0	Size of cable entries	M 40
Top part/bottom part/lid	upper part	Cover	without cover
Tightening torque	2 Nm	Number of cable entry on top	1
Number of cable entry sideways	0	Design of housing	Plug housing, Cable entry from top
Design of locking system	Side-locking clamp on lower side	Design	Standard
Installation size	10	Cable entry	w. thread
Type	Plug	Clamp version	Side-locking clamp
Sealing	no sealing	Internal thread	M 40
Colour (RAL)	RAL 7035	BG	10
Suitable for ModuPlug®	Yes		

**Classifications**

ETIM 8.0	EC000437	ETIM 9.0	EC000437
ETIM 10.0	EC000437	ECLASS 14.0	27-44-02-02
ECLASS 15.0	27-44-02-02		

**HDC 32B TOBU 1M40G**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)



## HDC 32B TOBU 1M40G

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

## Accessories

www.weidmueller.com

## Base housing



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

## General ordering data

Type	HDC 32B SBU 1M32G	Version
Order No.	<a href="#">1902600000</a>	HDC enclosures, Installation size: 10, Protection degree: IP65, in
GTIN (EAN)	4032248585625	plugged condition, Base housing, Side-locking clamp on lower side,
Qty.	1 ST	Standard, Size of cable entries: M 32
Type	HDC 32B SBU 2PG29G	Version
Order No.	<a href="#">1666920000</a>	HDC enclosures, Installation size: 10, Protection degree: IP65, in
GTIN (EAN)	4008190424121	plugged condition, Base housing, Side-locking clamp on lower side,
Qty.	1 ST	Standard, Size of cable entries: PG 29
Type	HDC 32B SBU 2M32G	Version
Order No.	<a href="#">1788460000</a>	HDC enclosures, Installation size: 10, Protection degree: IP65, in
GTIN (EAN)	4032248205998	plugged condition, Base housing, Side-locking clamp on lower side,
Qty.	1 ST	Standard, Size of cable entries: M 32
Type	HDC 32B SBU 1PG36G	Version
Order No.	<a href="#">1902610000</a>	HDC enclosures, Installation size: 10, Protection degree: IP65, in
GTIN (EAN)	4032248585632	plugged condition, Base housing, Side-locking clamp on lower side,
Qty.	1 ST	Standard, Size of cable entries: PG 36
Type	HDC 32B SBU 2PG36G	Version
Order No.	<a href="#">1902640000</a>	HDC enclosures, Installation size: 10, Protection degree: IP65, in
GTIN (EAN)	4032248585649	plugged condition, Base housing, Side-locking clamp on lower side,
Qty.	1 ST	Standard, Size of cable entries: PG 36

**HDC 32B TOBU 1M40G**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Accessories**

**Bulkhead housing**



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.  
 The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.  
 The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.  
 The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.  
 Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

**General ordering data**

Type	HDC 32B ABU	Version
Order No.	<a href="#">1217800000</a>	HDC enclosures, Installation size: 10, Protection degree: IP65, in
GTIN (EAN)	4008190148393	plugged condition, Bulkhead housing, Side-locking clamp on lower
Qty.	1 ST	side, Standard

**Coupling hood**



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.  
 The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.  
 The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.  
 The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.  
 Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

**General ordering data**

Type	HDC 32B KBU 1M40G	Version
Order No.	<a href="#">1902730000</a>	HDC enclosures, Installation size: 10, Protection degree: IP65, in
GTIN (EAN)	4032248585670	plugged condition, Coupling housing, Side-locking clamp on lower
Qty.	1 ST	side, Standard, Size of cable entries: M 40
Type	HDC 32B KBU 1PG29G	Version
Order No.	<a href="#">1902740000</a>	HDC enclosures, Installation size: 10, Protection degree: IP65, in
GTIN (EAN)	4032248585687	plugged condition, Coupling housing, Side-locking clamp on lower
Qty.	1 ST	side, Standard, Size of cable entries: PG 29

## HDC 32B TOBU 1M40G

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

Type	HDC 32B KBU 1PG36G	Version	
Order No.	<a href="#">1902750000</a>		HDC enclosures, Installation size: 10, Protection degree: IP65, in
GTIN (EAN)	4032248585694		plugged condition, Coupling housing, Side-locking clamp on lower
Qty.	1 ST		side, Standard, Size of cable entries: PG 36

### IP68 version



In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications. The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure. Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

### General ordering data

Type	VG M40 - MS 68	Version	
Order No.	<a href="#">1772250000</a>		VG MS (standard brass cable gland), Cable glands, straight, M 40, 9
GTIN (EAN)	4032248129904		mm, OD min. 18 - OD max. 25 mm, IP54, IP66, IP67, IP68 - 5 bar (30
Qty.	10 ST		min.), Brass, nickel-plated
Type	VG M40-1/K68	Version	
Order No.	<a href="#">1909890000</a>		VG K (standard plastic cable gland), Cable glands, straight, M 40, 10
GTIN (EAN)	4032248536818		mm, OD min. 19 - OD max. 28 mm, IP54, IP66, IP67, IP68 - 5 bar (30
Qty.	10 ST		min.), Polyamide 6