


FTA-C300-32DO-LD-S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Digital input/output direct FTAs for Honeywell C300 IOTAs.

Passive interfaces (FTA) for connecting the Honeywell C300 digital IOTAs.

- Clearly labelled: Same connector and position on the FTA and on the IOTA.
- The light indicator (LED) indicates the position of the switch.
- Possibility of feeding the IOTA from the FTA (fuse protected).
- Fuse protection per channel (optional).
- Screw or tension clamp connection.

General ordering data

Order No.	1221590000
Type	FTA-C300-32DO-LD-S
GTIN (EAN)	4050118005097
Qty.	1 items

FTA-C300-32DO-LD-S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E141197

Dimensions and weights

Depth	65 mm	Depth (inches)	2.5591 inch
Height	87 mm	Height (inches)	3.4252 inch
Width	216 mm	Width (inches)	8.5039 inch
Net weight	410 g		

Temperatures

Storage temperature	-40...60 °C	Operating temperature	-25...50 °C
---------------------	-------------	-----------------------	-------------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c, 7cl
REACH SVHC	Lead 7439-92-1
SCIP	2e4a427f-c282-4ebf-8ee2-8af7c9348f4e

Rated data UL

Rated current IN	1 A	Operating temperature UL, min.	0 °C
Operating temperature UL, max.	25 °C	Rated voltage UN	24 V DC
Rated voltage DC UN (supply)	24 V	Rated current (supply)	5 A
Rated current fuse (supply)	5 A		

General data

LED status display per channel	green	Type of test point	No
Fuse per channel	No	LED status of the supply voltage	yellow
Power supply fuse	5 A		

Connection data

Connection on control side	SLDV-THR 5.08
----------------------------	---------------

Ratings data

Operating voltage	24 V DC ± 10%	Max. current per channel	1 A
-------------------	---------------	--------------------------	-----

Insulation coordination (EN50178)

Rated insulation voltage	<50 V AC	Surge voltage category	III
Pollution severity level	2	Pulse voltage test (1,2/50µs)	0.8 kV
Insulation test voltage AC	0.35 kV		

FTA-C300-32DO-LD-S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data**Connection field**

Clamping range, max.	6 mm ²	Clamping range, min.	0.13 mm ²
----------------------	-------------------	----------------------	----------------------

Supply connection

Clamping range, min.	0.13 mm ²	Clamping range, max.	6 mm ²
----------------------	----------------------	----------------------	-------------------

Classifications

ETIM 8.0	EC002780	ETIM 9.0	EC002780
ETIM 10.0	EC002780	ECLASS 14.0	27-14-11-52
ECLASS 15.0	27-14-11-52		

FTA-C300-32DO-LD-S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

