

**TW PRV4 A-D****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

The comprehensive accessories of the Klippon® Connect portfolio are perfectly matched down to the last detail. This facilitates mounting while adhering to required norms

**General ordering data**

|            |  |
|------------|--|
| Version    | P-series, Partition plate, grey, 2 mm, Printed A-D, horizontally |
| Order No.  | <a href="#">1230070000</a>                                       |
| Type       | TW PRV4 A-D  |
| GTIN (EAN) | 4050118013764  |
| Qty.       | 10 items   |

## TW PRV4 A-D

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS Conform

## Dimensions and weights

|            |         |                 |             |
|------------|---------|-----------------|-------------|
| Depth      | 41.1 mm | Depth (inches)  | 1.6181 inch |
| Height     | 70 mm   | Height (inches) | 2.7559 inch |
| Width      | 2 mm    | Width (inches)  | 0.0787 inch |
| Net weight | 4.63 g  |                 |             |

## Temperatures

|                                  |                |                                  |               |
|----------------------------------|----------------|----------------------------------|---------------|
| Storage temperature              | -25 °C...55 °C | Ambient temperature              | -5 °C...40 °C |
| Continuous operating temp., min. | -50 °C         | Continuous operating temp., max. | 125 °C        |

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## Material data

|                           |               |        |      |
|---------------------------|---------------|--------|------|
| Basic material            | Polycarbonate | Colour | grey |
| UL 94 flammability rating | V-0           |        |      |

## System specifications

|         |                           |                  |   |
|---------|---------------------------|------------------|---|
| Version | Printed A-D, horizontally | Number of levels | 4 |
|---------|---------------------------|------------------|---|

## Additional technical data

|         |     |
|---------|-----|
| Snap-on | Yes |
|---------|-----|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000886    | ETIM 9.0    | EC000886    |
| ETIM 10.0   | EC000886    | ECLASS 14.0 | 27-25-03-01 |
| ECLASS 15.0 | 27-25-03-01 |             |             |

