

TW PRV8 1-8**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

The comprehensive accessories of the Klippon® Connect portfolio are perfectly matched down to the last detail. This facilitates mounting while adhering to required norms

General ordering data

| | |
|------------|--|
| Version | P-series, Partition plate, grey, 2 mm, Printed 1-8, horizontally |
| Order No. | 1230080000 |
| Type | TW PRV8 1-8 |
| GTIN (EAN) | 4050118013740 |
| Qty. | 10 items |

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 59.7 mm | Depth (inches) | 2.3504 inch |
| Height | 120 mm | Height (inches) | 4.7244 inch |
| Width | 2 mm | Width (inches) | 0.0787 inch |
| Net weight | 9.67 g | | |

Temperatures

| | | | |
|----------------------------------|----------------|----------------------------------|----------------|
| Storage temperature | -25 °C...55 °C | Ambient temperature | -50 °C...80 °C |
| Continuous operating temp., min. | -50 °C | Continuous operating temp., max. | 125 °C |

Environmental Product Compliance

| | | | |
|--------------------------|-----------------------------|------------------|--|
| RoHS Compliance Status | Compliant without exemption | | |
| REACH SVHC | No SVHC above 0.1 wt% | | |
| Product Carbon Footprint | Cradle to gate | 0.067 kg CO2 eq. | |

Material data

| | | | |
|---------------------------|---------------|--------|------|
| Basic material | Polycarbonate | Colour | grey |
| UL 94 flammability rating | V-0 | | |

System specifications

| | | | |
|---------|---------------------------|------------------|---|
| Version | Printed 1-8, horizontally | Number of levels | 8 |
|---------|---------------------------|------------------|---|

Additional technical data

| | |
|---------|-----|
| Snap-on | Yes |
|---------|-----|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000886 | ETIM 9.0 | EC000886 |
| ETIM 10.0 | EC000886 | ECLASS 14.0 | 27-25-03-01 |
| ECLASS 15.0 | 27-25-03-01 | | |

Drawings

