

**TW PRV16 1-16**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Product image**

The comprehensive accessories of the Klippon® Connect portfolio are perfectly matched down to the last detail. This facilitates mounting while adhering to required norms

**General ordering data**

|            |                                                                   |
|------------|-------------------------------------------------------------------|
| Version    | P-series, Partition plate, grey, 2 mm, Printed 1-16, horizontally |
| Order No.  | <a href="#">1230120000</a>                                        |
| Type       | TW PRV16 1-16                                                     |
| GTIN (EAN) | 4050118013924                                                     |
| Qty.       | 10 items                                                          |

**Technical data**

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Dimensions and weights**

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Depth      | 100 mm | Depth (inches)  | 3.937 inch  |
| Height     | 225 mm | Height (inches) | 8.8582 inch |
| Width      | 2 mm   | Width (inches)  | 0.0787 inch |
| Net weight | 26.4 g |                 |             |

**Temperatures**

|                                  |                |                                  |               |
|----------------------------------|----------------|----------------------------------|---------------|
| Storage temperature              | -25 °C...55 °C | Ambient temperature              | -5 °C...40 °C |
| Continuous operating temp., min. | -50 °C         | Continuous operating temp., max. | 125 °C        |

**Environmental Product Compliance**

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

**Material data**

|                           |               |        |      |
|---------------------------|---------------|--------|------|
| Basic material            | Polycarbonate | Colour | grey |
| UL 94 flammability rating | V-0           |        |      |

**System specifications**

|         |                            |                  |    |
|---------|----------------------------|------------------|----|
| Version | Printed 1-16, horizontally | Number of levels | 16 |
|---------|----------------------------|------------------|----|

**Additional technical data**

|         |     |
|---------|-----|
| Snap-on | Yes |
|---------|-----|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000886    | ETIM 9.0    | EC000886    |
| ETIM 10.0   | EC000886    | ECLASS 14.0 | 27-25-03-01 |
| ECLASS 15.0 | 27-25-03-01 |             |             |

**Drawings**

