

**IE-SFP-1GLXLC****Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Product image**

- Supports DDM (Digital Diagnostic Monitoring)
- IEEE 802.3z compliant (Gigabit Ethernet SFPs)
- IEEE 802.3u compliant (Fast Ethernet SFPs)
- Symmetric LVPECL I/Os (Gigabit Ethernet SFPs)
- Symmetric PECL I/Os (Fast Ethernet SFPs)
- TTL signal detection indicator
- Pluggable in operation (hot pluggable)
- Class 1 laser product, EN60825-1 compliant
- Applicable for switches of the Basic-, Value- and PremiumLine

**General ordering data**

Version	SFP Transceiver, 1000 Mbps, Singlemode, LC-Duplex, 10 km, 0 °C...60 °C
Order No.	<a href="#">1241510000</a>
Type	IE-SFP-1GLXLC
GTIN (EAN)	4050118029338
Qty.	1 items

**IE-SFP-1GLXLC**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate No. (cURus)	E230683

**Dimensions and weights**

Net weight	35 g
------------	------

**Temperatures**

Storage temperature	-40 °C...85 °C	Operating temperature	0 °C...60 °C
Humidity	5 to 95 % (non-condensing)		

**Environmental Product Compliance**

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	7cl
REACH SVHC	No SVHC above 0.1 wt%

**EMC conformity and approvals**

EMC standards	EN 55032, EN 55035	Ship use	DNV
Safety standard	UL 62368-1, EN 62368-1, EN 60825-1		

**Environmental conditions**

Operating temperature, max.	60 °C	Operating temperature, min.	0 °C
Humidity	5 to 95 % (non-condensing)	Storage temperature, max.	85 °C
Storage temperature, min.	-40 °C		

**Fibre optic transceiver characteristics**

Transmission rate	1000 Mbps	
Digital diagnostic monitor function (DDM)	Supported	
Transceiver type	Singlemode	
Connector type	LC-Duplex	
Transmission distance, typ.	10 km	
Wavelength	typ.	1310 nm
	Wavelength	TX
	min.	1280 nm
	max.	1355 nm
	Wavelength	RX
	min.	1260 nm
Receive power	min.	-21 dBm
	max.	-3 dBm
Transmission power	min.	-9 dBm

**IE-SFP-1GLXLC**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

Link-budget	max. 12 dB	-3 dBm
-------------	------------	--------

**Guarantee**

Time interval	3 years
---------------	---------

**Interfaces**

Ethernet ports	1	Plug-in connector	Duplex-LC
----------------	---	-------------------	-----------

**Power supply**

Supply voltage	3.3 V (via Ethernet switch)
----------------	-----------------------------

**Technical data**

Type of mounting	Insert in SFP slot
------------------	--------------------

**Classifications**

ETIM 8.0	EC003628	ETIM 9.0	EC003628
ETIM 10.0	EC003628	ECLASS 14.0	19-17-03-03
ECLASS 15.0	19-17-03-03		