


MF 5/12 MC SDR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



Similar to illustration



MultiFit is the Weidmüller marker system used for other makes of terminals. Similar to the Weidmüller Dekafix, the markers of the MultiFit family are available ready-for-use with standard printing.

We recommend to carry out a test with sample markers on the terminals used when using MultiFit for the first time.

- One marker, suitable for different makes of terminals.
- Ready-to-use markers with standard printing
- Blank markers for printing with the PrintJet CONNECT or Plotter
- Delivery of individually printed markers according to customer CAE data or specifications
- One marking system for all applications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | |
|------------|--|
| Version | MultiFit, Terminal marker, 5 x 12 mm, Pitch in mm (P): 4.00 Phoenix, To customer specification |
| Order No. | 1250080000 |
| Type | MF 5/12 MC SDR |
| GTIN (EAN) | 4050118040708 |
| Qty. | 50 items |

MF 5/12 MC SDR

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 1.6 mm | Depth (inches) | 0.063 inch |
| Height | 5 mm | Height (inches) | 0.1968 inch |
| Width | 12 mm | Width (inches) | 0.4724 inch |
| Net weight | 0.33 g | | |

Temperatures

Operating temperature range -40...100 °C

Environmental Product Compliance

| | | | |
|--------------------------|-----------------------------|------------------|--|
| RoHS Compliance Status | Compliant without exemption | | |
| REACH SVHC | No SVHC above 0.1 wt% | | |
| Product Carbon Footprint | Cradle to gate | 0.002 kg CO2 eq. | |

General data

| | | | |
|--------------------------------------|-------------------------------|-----------|--|
| Printing method | MC Laser | | |
| Width | 12 mm | | |
| UL 94 flammability rating | V-2 | | |
| Operating temperature range, max. | 100 °C | | |
| Operating temperature range, min. | -40 °C | | |
| Colour | To customer specification | | |
| Halogen | No | | |
| Basic material | Polyamide 66 | | |
| Colour of printing | black | | |
| Printed characters | Requires M-Print PRO File | | |
| Number of markers per packaging unit | Form of supply | MultiCard | |
| Number of markers per combination | 1 MultiCard = Terminal marker | | |
| Operating temperature range | -40...100 °C | | |
| Application/manufacturer | Phoenix | | |


Connector markers

Pitch in mm (P) 4.00 mm

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000761 | ETIM 9.0 | EC000761 |
| ETIM 10.0 | EC000761 | ECLASS 14.0 | 27-28-11-01 |
| ECLASS 15.0 | 27-28-11-01 | | |

Drawings



Similar to illustration

Drawing

