

KLBUE 15-32 FM4**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



With our wide range of KLBÜ shield connections, you can achieve flexible and self-adjusting shield contacting and ensure error-free plant operation.

General ordering data

Version	Clamping yoke, Clamping yoke for shield connection
Order No.	1252490000
Type	KLBUE 15-32 FM4
GTIN (EAN)	4032248112524
Qty.	10 items

KLBUE 15-32 FM4

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	64 mm	Depth (inches)	2.5197 inch
Height	50.5 mm	Height (inches)	1.9882 inch
Width	34.5 mm	Width (inches)	1.3583 inch
Net weight	82.4 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
Continuous operating temp., min.	-60 °C	Continuous operating temp., max.	130 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption		
REACH SVHC	No SVHC above 0.1 wt%		
Product Carbon Footprint	Cradle to gate	0.228 kg CO2 eq.	

Material data

Colour	silver	UL 94 flammability rating	None
--------	--------	---------------------------	------

System specifications

End cover plate required	No	Mounting rail	TS 35
--------------------------	----	---------------	-------

Additional technical data

Installation advice	TS 35	Explosion-tested version	No
Type of mounting	Snap-on		

Conductors for clamping (rated connection)

Stripping length	32 mm	Type of connection	Spring connection
Number of connections	1	Cable diameter, max.	32 mm
Cable diameter, min.	15 mm	Connection cross-section, stranded, max.	32 mm ²
Connection cross-section, stranded, min. 15 mm ²			

General

Installation advice	TS 35	Mounting rail	TS 35
---------------------	-------	---------------	-------

Rating data

Rated cross-section	32 mm ²
---------------------	--------------------

Classifications

ETIM 8.0	EC002020	ETIM 9.0	EC002020
ETIM 10.0	EC002020	ECLASS 14.0	27-25-01-20
ECLASS 15.0	27-25-01-20		