

KLBUE 10-20 CPF16**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

With our wide range of KLBÜ shield connections, you can achieve flexible and self-adjusting shield contacting and ensure error-free plant operation.

General ordering data

Version	Clamping yoke, Clamping yoke for shield connection, Steel
Order No.	1252550000
Type	KLBUE 10-20 CPF16
GTIN (EAN)	4050118104431
Qty.	10 items

KLBUE 10-20 CPF16

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	39.5 mm	Depth (inches)	1.5551 inch
Height	26 mm	Height (inches)	1.0236 inch
Width	25 mm	Width (inches)	0.9842 inch
Mounting dimension - width	24 mm	Net weight	43.3 g

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
Continuous operating temp., min.	-60 °C	Continuous operating temp., max.	130 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption		
REACH SVHC	No SVHC above 0.1 wt%		
Product Carbon Footprint	Cradle to gate	0.097 kg CO2 eq.	

Material data

Basic material	Steel	Colour	grey
UL 94 flammability rating	None		

System specifications

End cover plate required	No	Mounting rail	TS 27
--------------------------	----	---------------	-------

Additional technical data

Type of fixing	Snap-on	Installation advice	Direct mounting
Explosion-tested version	No	Type of mounting	Screw

Conductors for clamping (rated connection)

Stripping length	26 mm	Type of connection	Spring connection
Number of connections	1	Cable diameter, max.	20 mm
Cable diameter, min.	10 mm	Connection cross-section, stranded, max.	20 mm ²
Connection cross-section, stranded, min. 10 mm ²			

Dimensions

Pitch in mm (P)	25.00 mm
-----------------	----------

General

Installation advice	Direct mounting	Mounting rail	TS 27
---------------------	-----------------	---------------	-------

Rating data

Rated cross-section	20 mm ²
---------------------	--------------------

KLBUE 10-20 CPF16**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Classifications**

ETIM 8.0	EC002020	ETIM 9.0	EC002020
ETIM 10.0	EC002020	ECLASS 14.0	27-25-01-20
ECLASS 15.0	27-25-01-20		