

KTB GP 26XX15 CD S4 6MM**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com


Similar to illustration

Abbildung ähnlich

Integrate, expand and customise: The ideal expansion for every application

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

Flange plates

Flange plates in two thicknesses, for easy replacement of pre-assembl

General ordering data

Version	Klippon TB (Terminal Box), flange plate, straight, Height: 208 mm, Width: 117 mm, Depth: 6 mm, Gland plates: left, right, Basic material: Stainless steel 1.4404, electropolished, silver
Order No.	1256310000
Type	KTB GP 26XX15 CD S4 6MM
GTIN (EAN)	4050118093728
Qty.	1 items

KTB GP 26XX15 CD S4 6MM

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	6 mm	Depth (inches)	0.2362 inch
Height	208 mm	Height (inches)	8.189 inch
Width	117 mm	Width (inches)	4.6063 inch
Net weight	1050 g		

Temperatures

Operating temperature

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General information

Material thickness	6 mm	Installation advice	Screw mounting
Surface finish	electropolished	Basic material	Stainless steel 1.4404
Integral fixing	Screwed	Protection class (UL)	Type 3, Type 4X, Type 12
Gland plates	left, right	Flange plate	Yes
Areas of use	Explosive risk zone, Process industry		

General information on accessories

Material thickness	6 mm	Surface finish	electropolished
Basic material	Stainless steel 1.4404		

Classifications

ETIM 8.0	EC000211	ETIM 9.0	EC000211
ETIM 10.0	EC000211	ECLASS 14.0	27-14-24-21
ECLASS 15.0	27-14-24-21		