

**KTB GP XX2615 AB S4 6MM**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Similar to illustration**

Abbildung ähnlich

Integrate, expand and customise: The ideal expansion for every application

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

Flange plates

Flange plates in two thicknesses, for easy replacement of pre-assembl

**General ordering data**

Version	Klippon TB (Terminal Box), flange plate, straight, Height: 254 mm, Width: 117 mm, Depth: 6 mm, Gland plates: top, Bottom, Basic material: Stainless steel 1.4404, electropolished, silver
Order No.	<a href="#">1256380000</a>
Type	KTB GP XX2615 AB S4 6MM
GTIN (EAN)	4050118093797
Qty.	1 items

**KTB GP XX2615 AB S4 6MM**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth	6 mm	Depth (inches)	0.2362 inch
Height	254 mm	Height (inches)	10 inch
Width	117 mm	Width (inches)	4.6063 inch
Net weight	1400 g		

**Temperatures**

Operating temperature

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**General information**

Material thickness	6 mm	Surface finish	electropolished
Basic material	Stainless steel 1.4404	Integral fixing	Screwed
Protection class (UL)	Type 3, Type 4X, Type 12	Gland plates	top, Bottom
Flange plate	Yes	Areas of use	Explosive risk zone, Process industry

**General information on accessories**

Material thickness	6 mm	Surface finish	electropolished
Basic material	Stainless steel 1.4404		

**Classifications**

ETIM 8.0	EC000211	ETIM 9.0	EC000211
ETIM 10.0	EC000211	ECLASS 14.0	27-14-24-21
ECLASS 15.0	27-14-24-21		