

KTB GP XX3815V AB S4 6MM**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

Abbildung ähnlich

Integrate, expand and customise: The ideal expansion for every application

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

Flange plates

Flange plates in two thicknesses, for easy replacement of pre-assembl

General ordering data

Version	Klippon TB (Terminal Box), flange plate, straight, Height: 376 mm, Width: 117 mm, Depth: 6 mm, Gland plates: top, Bottom, Basic material: Stainless steel 1.4404, electropolished, silver
Order No.	1256480000
Type	KTB GP XX3815V AB S4 6MM
GTIN (EAN)	4050118093865
Qty.	1 items

KTB GP XX3815V AB S4 6MM
Weidmüller Interface GmbH & Co. KG

 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com
Technical data
Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	6 mm	Depth (inches)	0.2362 inch
Height	376 mm	Height (inches)	14.8031 inch
Width	117 mm	Width (inches)	4.6063 inch
Net weight	2100 g		

Temperatures

Operating temperature

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General information

Material thickness	6 mm	Installation advice	Screw mounting
Surface finish	electropolished	Basic material	Stainless steel 1.4404
Integral fixing	Screwed	Protection class (UL)	Type 3, Type 4X, Type 12
Gland plates	top, Bottom	Flange plate	Yes
Areas of use	Transportation, Explosive risk zone		

General information on accessories

Material thickness	6 mm	Solder eyelet hole diameter (D)	7 mm
Surface finish	electropolished	Basic material	Stainless steel 1.4404

Classifications

ETIM 8.0	EC000211	ETIM 9.0	EC000211
ETIM 10.0	EC000211	ECLASS 14.0	27-14-24-21
ECLASS 15.0	27-14-24-21		