

KTB GP 765020 CD S4 6MM**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

Abbildung ähnlich

Integrate, expand and customise: The ideal expansion for every application

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

Flange plates

Flange plates in two thicknesses, for easy replacement of pre-assembl

General ordering data

Version	Klippon TB (Terminal Box), flange plate, straight, Height: 341 mm, Width: 167 mm, Depth: 6 mm, Gland plates: left, right, Basic material: Stainless steel 1.4404, electropolished, silver
Order No.	1256690000
Type	KTB GP 765020 CD S4 6MM
GTIN (EAN)	4050118094015
Qty.	1 items
Delivery status	Discontinued
Available until	2024-10-31T00:00:00+01:00
Alternative product	KTB GP 76XX20V CD S4 6MM

KTB GP 765020 CD S4 6MM

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data
Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	6 mm	Depth (inches)	0.2362 inch
Height	341 mm	Height (inches)	13.4252 inch
Width	167 mm	Width (inches)	6.5748 inch
Net weight	2720 g		

Temperatures

Operating temperature

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General information

Material thickness	6 mm	Surface finish	electropolished
Basic material	Stainless steel 1.4404	Protection class (UL)	Type 3, Type 4X, Type 12
Gland plates	left, right		

General information on accessories

Material thickness	6 mm	Surface finish	electropolished
Basic material	Stainless steel 1.4404		

Classifications

ETIM 8.0	EC000211	ETIM 9.0	EC000211
ETIM 10.0	EC000211	ECLASS 14.0	27-14-24-21
ECLASS 15.0	27-14-24-21		