

**ADAPS M32-M40-W****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



ADAP series adaptors provide flexibility and versatility infilling unused entries in Ex equipment while maintaining Flameproof Ex d and Increased Safety Ex e explosion protection and IP66/67/68 ingress rate.

**General ordering data**

Version	ADAP (Klippon Ex adaptor), Adapter, straight, M 32 ,M 40, Stainless steel 1.4404
Order No.	<a href="#">1261970000</a>
Type	ADAPS M32-M40-W
GTIN (EAN)	4050118093018
Qty.	12 items

**ADAPS M32-M40-W**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



ROHS Conform

**Dimensions and weights**

Width	51 mm	Width (inches)	2.0079 inch
Length	39 mm	Length (inches)	1.5354 inch
Net weight	156 g		

**Temperatures**

Operating temperature -50 °C...120 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant without exemption  
 REACH SVHC No SVHC above 0.1 wt%

**Certificate numbers cable gland**

Identification	II 2G 1D, Ex db IIC Gb, Ex eb IIC Gb, Ex ta IIIC Da	Certificate no. cable gland (ATEX)	TÜV IT 16ATEX 059X
Certificate no. cable gland (IECEX)	IECEX TPS 16.0004X	Certificate no. cable gland (CCC)	2020322313000069
Certificate No. (IECEX)	IECEXTPS 16.0004X		

**General information**

Outer cable diameter, max.	24 mm	Outer cable diameter, min.	1 mm
O-Ring	Silicone	Tightening torque	65 Nm
Silicone	Yes	Operating temperature range, max.	120 °C
Operating temperature range, min.	-50 °C	Pitch of thread	1.5 mm
Halogen	halogen-free	Standards	EN 60079-0, EN 60079-1, EN 60079-31, EN 60079-7, IEC 60079-0, IEC 60079-1, IEC 60079-31, IEC 60079-7, GB 12476.1, GB 12476.5, GB 3836.1, GB 3836.2, GB 3836.3
AF size 1	46 mm	Protection degree	IP66
Cable gland	M 32	Basic material	Stainless steel 1.4404
External thread	M 32	Internal thread	M 40
Length of thread	16 mm	Explosion protection type	Ex d - flameproof, Ex e - increased safety
Installation guidelines	See assembly instructions		

**Classifications**

ETIM 8.0	EC000441	ETIM 9.0	EC000441
ETIM 10.0	EC000441	ECLASS 14.0	27-14-08-06
ECLASS 15.0	27-14-08-06		

## ADAPS M32-M40-W

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

## Nylon flat washer - GWDR



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

## General ordering data

Type	GWDR M32-W	Version	
Order No.	<a href="#">1185630000</a>		in closed state, M 32, Nylon 6
GTIN (EAN)	4050118078329		
Qty.	160 ST		

## Stainless Steel lock nuts, natural finish



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

## General ordering data

Type	SKMUS M32-W	Version	
Order No.	<a href="#">1185710000</a>		SKMU SS (stainless steel locknut), Locknut, M 32, 3.8 mm, Stainless steel 1.4404
GTIN (EAN)	4050118233759		
Qty.	144 ST		